




RESISTANCE @ +25°C = 100,000 Ω NOMINAL
 ACCURACY (0 TO +70°C) = ± 0.10°C
 RESISTANCE/TEMPERATURE CURVE = "R"
 TEMPERATURE COEFFICIENT @ +25°C = -4.68%/°C NOMINAL
 BETA "β" (0 TO +50°C) = 4,140°K NOMINAL
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (STILL AIR)
 THERMAL TIME CONSTANT = 1 SECOND MAXIMUM (WELL STIRRED OIL)
 MAXIMUM TEMPERATURE RATING = +150°C

MAXIMUM STORAGE AND OPERATION TEMPERATURE FOR BEST LONG-TERM STABILITY = +75°C

REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	03/23/05	DD

SCALE	NONE	© COPYRIGHT	
DRAWN BY	DAN DANKERT	U.S. SENSOR CORP.	
DATE	08/28/97	714-639-1000 www.ussensor.com	
REV.	NONE	NTC THERMISTOR	
LAYER	0 OF 1	P/N	PS104R2