


RESISTANCE @ +25°C = 50,000 Ω NOMINAL
ACCURACY (0 TO +70°C) = ± 0.50°C
RESISTANCE/TEMPERATURE CURVE = "R"
TEMPERATURE COEFFICIENT @ +25°C = −4.68%/°C NOMINAL
BETA "β" (0 TO +50°C) = 4,140°K NOMINAL
DISSIPATION CONSTANT = 1 mW/°C NOMINAL
THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (STILL AIR)
THERMAL TIME CONSTANT = 1 SECOND MAXIMUM (WELL STIRRED OIL)
MAXIMUM TEMPERATURE RATING = +135°C

MAXIMUM STORAGE AND OPERATION TEMPERATURE FOR BEST LONG-TERM STABILITY = +120°C

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	05/01/03	DD

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 05/01/03

REV. NONE

LAYER 0 OF 1

© COPYRIGHT

U.S. SENSOR CORP.
714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N KW503R2