



RESISTANCE @ +25°C = 10,000 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = "E1"
BETA "β" (+25 TO +85°C) = 3,435°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = −3.52%/°C NOMINAL
DISSIPATION CONSTANT = 0.45 mW/°C NOMINAL (AIR)
THERMAL TIME CONSTANT = 2.5 SECONDS NOMINAL (AIR)
MAXIMUM TEMPERATURE RATING = +260°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

| REV | REVISION RECORD | DATE | APP |
|---|---|---|---|
| | | | |
| NONE | RELEASE TO PRODUCTION | 04/03/14 | DD |

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 04/03/14

REV. NONE

LAYER 0 OF 2

U.S. SENSOR CORP.

© COPYRIGHT

714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N GT103E1K