


RESISTANCE @ 0°C = 1,000 Ω ± 0.06%
ACCURACY @ 0°C = ± 0.15°C
ACCURACY CLASS = DIN EN 60751 F 0.15
TCR = 3,850 ppm/°C
TEMPERATURE RATING = -200 TO +600°C
THERMAL TIME CONSTANT = 1.2 SECONDS NOMINAL (AIR 1 m/SECOND)
DISSIPATION CONSTANT = 1.8 mW/°C NOMINAL (AIR)

SEE MANUFACTURING SPECIFICATION (LAYER 1)

REV	REVISION RECORD	DATE	APP
"C"	CLARIFIED ACCURACY CLASS	06/30/17	DD
"B"	CHANGED DIMENSION TOLERANCES	03/22/12	DD
"A"	ADDED SUBSTRATE THICKNESS DIMENSION (0.00984" ± 0.006")	02/12/07	DD
NONE	RELEASE TO PRODUCTION	12/15/06	DD

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 12/15/06

REV. "C"

LAYER 0 OF 2

U.S. SENSOR CORP.

© COPYRIGHT

714-639-1000 www.ussensor.com

PLATINUM RTD SENSOR

P/N PPG102A6