


RESISTANCE @ +25°C = 100,000 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = "L1"
BETA "β" (+25 TO +85°C) = 4,040°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = −4.52%/°C NOMINAL
DISSIPATION CONSTANT = 0.45 mW/°C NOMINAL (AIR)
THERMAL TIME CONSTANT = 2.5 SECONDS NOMINAL (AIR)
MAXIMUM TEMPERATURE RATING = +300°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	02/20/14	DD

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 02/20/14

REV. NONE

LAYER 0 OF 2

U.S. SENSOR CORP.

© COPYRIGHT

714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N GT104L1K