


RESISTANCE @ 0°C = 1,000 Ω ± 0.06%
ACCURACY @ 0°C = ± 0.15°C
ACCURACY CLASS = DIN EN 60751 F 0.15
TCR = 3,850 ppm/°K
TEMPERATURE RATING = -200 TO +600°C
THERMAL TIME CONSTANT = 2 SECONDS NOMINAL (AIR 1 m/SECOND)
DISSIPATION CONSTANT = 2.2 mW/°C NOMINAL (AIR)

SEE MANUFACTURING SPECIFICATION (LAYER 1)

REV	REVISION RECORD	DATE	APP
"A"	CLARIFIED ACCURACY CLASS	06/30/17	DD
NONE	RELEASE TO PRODUCTION	03/12/12	DD

SCALE NONE	© COPYRIGHT U.S. SENSOR CORP.
DRAWN BY DAN DANKERT	714-639-1000 www.ussensor.com
DATE 03/12/12	PLATINUM RTD SENSOR
REV. "A"	P/N PPG102A5
LAYER 0 OF 2	