


RESISTANCE @ +25°C = 500,000 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = "R"
BETA "β" (0 TO +50°C) = 4,140°K NOMINAL
TEMPERATURE COEFFICIENT @ +25°C = −4.68%/°C NOMINAL
DISSIPATION CONSTANT = 2 mW/°C NOMINAL
THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM
MAXIMUM TEMPERATURE RATING = +220°C

*** ROHS COMPLIANT ***

PACKAGING: BULK

REV	REVISION RECORD	DATE	APP
NONE	RELEASE TO PRODUCTION	01/27/14	DD
"A"	CHANGED DIMENSIONS	01/27/14	DD

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 10/04/01

REV. "A"

LAYER 0 OF 1

U.S. SENSOR CORP.

www.ussensor.com 714-639-1000

© COPYRIGHT

NTC THERMISTOR

P/N SM504R1K