Specification Status: Released

Electrical Rating

Voltage: 16V_{DC} MAX
Current: 40A MAX

Insulating Material:
Cured, Flame Retardant Epoxy Polymer
meets UL 94 V-O Requirements

Lead Material:
24 AWG Tin Plated Copper Clad Steel

Marking:

XX R250 — Manufacturer's Mark and Part Identification

□□□□ — Lot Identification




TABLE I. DIMENSIONS:

	A		B		C		D		E	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	--	11.4	--	18.3	4.3	5.8	7.6	--	--	3.0
in*:	--	(0.45)	--	(0.72)	(0.17)	(0.23)	(0.30)	--	--	(0.12)

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS :

I HOLD RATED CURRENT	CURRENT RATINGS		INITIAL RESISTANCE VALUES			ONE HOUR POST-TRIP RESISTANCE STANDARD TRIP	TIME TO TRIP @ 8A	TRIPPED-STATE POWER DISSIPATION
AMPERS AT 20°C	AMPERES AT 20°C		OHMS AT 20°C			OHMS AT 20°C	SECONDS AT 20°C	WATTS AT 20°C
HOLD	HOLD	TRIP	MIN	TYP	MAX	MAX		
2.50	2.50	5.00	0.02	0.03	0.036	0.06	40	1.2

Agency Recognitions: UL, CSA, TUV
Reference Documents: PS300
Precedence: This specification takes precedence over documents referenced herein.
Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.
CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant — Directive 2002/95/EC Compliant
ELV Compliant — Directive 2000/53/EC Compliant
Pb-Free
Halogen Free*

* Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm.

© 2016 Littelfuse,Inc.
Specifications are subject to change without notice
Revised July 26,2016

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

© 2016 Littelfuse,Inc.
Specifications are subject to change without notice
Revised July 26,2016