




RESISTANCE @ +25°C = 10,000 Ω ± 1%
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 MAXIMUM TEMPERATURE RATING = +80°C

MOISTURE RESISTANT PROBE ASSEMBLY

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	04/02/10	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR corp. 1832 W. COLL INS AVE. ORANGE, CA. 92867 714-639-1000 www.ussensor.com NTC THERMISTOR PROBE P/N USP10982
DRAWN BY	DAN DANKERT	
DATE	04/02/10	
REV.	NONE	
LAYER	0 OF 2	