




MM IN  
 6.85 .270  
 13.30 .524  
 13.46 .530  
 19.05 .750  
 33.52 1.320  
 39.14 1.541



- NOTES:
1. SILVERED CONTACTS.
  2. ALL STEEL PARTS PLATED.
  3. 25 AMPS @ 12 V.D.C.
  4. FACE NUT ASSEMBLED.

METRIC





DO NOT SCALE

EX21032A  
 BRUNING 40-21 63765

LET.	WAS	DATE	BY	LET.	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRVD.	SCALE	DATE DRAWN
								—//—	VAK			1:1	3/25/86
								FINISH					DATE BLUEPRINT
				A	DATE CODE	8-22-86	ZU	TOLERANCES	SW. TOGGLE S.P.S.T. 59024-12				
					ISSUED	7-15-86	AF	DECIMAL ± METRIC ±					

59024-13

MM	IN
6.85	.270
13.30	.524
13.46	.530
19.05	.750
33.52	1.320
39.14	1.541



- NOTES:
1. SILVERED CONTACTS.
  2. ALL STEEL PARTS PLATED.
  3. 25 AMPS @ 12 V.D.C.
  4. FACE NUT ASSEMBLED

METRIC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
								— # —	VAK			1:1	3/25/86
								FINISH	Cole Hersee Co. <small>WORLD BLDG. 4TH FLOOR SOUTH BOSTON MA 02111</small>				DATE BLUEPRINT
								— # —					
								TOLERANCES	SW. TOGGLE S.P.D.T.				59024-13
								DECIMAL ±					
								METRIC ±					
					ISSUED	8-28-86	A						


EX21032B

BRUN: VG 40-21 63765


CH-188(4-78)

59024-14


MM	IN
6.85	270
13.30	524
13.46	530
19.05	750
33.52	320
39.14	1541



FACE NUT



TOGGLE



- NOTES
- 1 SILVERED CONTACTS
  - 2 ALL STEEL PARTS PLATED.
  - 3 25 AMPS @ 12 VDC
  - 4 FACE NUT ASSEMBLED

METRIC

DO NOT SCALE


BRUNING 40-21 63765

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
								—	VAK			1:1	3/25/86
								FINISH	 <b>Cole Hersee Co.</b> <small>1901 COLONY ROAD SOUTH BOSTON MA 02125</small>				DATE BLUEPRINT
								TOLERANCES					
								DECIMAL ±	<b>SW. TOGGLE DP ST.</b>				<b>59024-14</b>
								METRIC ±					
								ISSUED	9286				

CH 188(4 78)

59024-15

MM IN  
 6.85 270  
 13.30 524  
 13.46 530  
 19.05 750  
 33.52 1320  
 39.14 1541



EX21032D

- NOTES:
1. SILVERED CONTACTS.
  2. ALL STEEL PARTS PLATED.
  3. 25 AMPS @ 12 V.D.C.
  4. FACE NUT ASSEMBLED

METRIC

DO NOT SCALE


BRUNING 40-21 63765

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D	SCALE	DATE DRAWN
								—	VAK			1:1	9-8-86
								FINISH	 Cole Hersee Co. <small>30 OLD COLONY STREET BOSTON MA U.S.A.</small>				DATE BLUEPRINT
								TOLERANCES					SW. TOGGLE DPDT.
								DECIMAL ±					
								METRIC ±					

CH 188(4 78)

59024-16


MM	IN
6.85	.270
13.30	.524
13.46	.530
19.05	.750
33.52	1.320
39.14	1.541



FACE NUT



TOGGLE



- NOTES:
1. SILVERED CONTACTS.
  2. ALL STEEL PARTS PLATED.
  3. 25 AMPS @ 12 V.D.C.
  4. FACE NUT ASSEMBLED

METRIC

DO NOT SCALE

BRUNING 40-21 63765


LET.	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRVD	SCALE	DATE DRAWN
								—//—	YAK	✓		1:1	9/10/86
								FINISH	 <b>Cole Hersee Co.</b> <small>WORLD CO. DIV. AFFAIR SOUTH BOSTON MA. U.S.A. 02111</small>				DATE BLUEPRINT
								TOLERANCES					
								DECIMAL ±	<b>SW. TOGGLE, D.P.S.T., MOM. 59024-16</b>				
								METRIC ±					
								ISSUED	7-10-86				

CH-188(4-78)


59024-33

MM	IN
0.96	0.038
1.82	0.072
2.51	0.099
2.56	0.101
3.97	0.156
5.02	0.198
5.13	0.202
6.35	0.250
8.63	0.340
8.76	0.345
10.31	0.406
13.30	0.524
13.46	0.530
19.05	0.750
20.70	0.815
20.83	0.820
33.52	1.320
39.14	1.541
41.40	1.630
41.65	1.640
44.62	1.756

98164 FACE NUT



TOP VIEW OF TOGGLE



- NOTES:
1. SILVER CONTACTS
  2. 25 AMPS @ 12VDC LAMP LOAD
  3. ALL STEEL PARTS PLATED
  4. FACE NUT ASSEMBLED
  5. PHENOLIC CONTACT PINS


METRIC

DO NOT SCALE  
CAD GENERATED

LET.	WAS	DATE	BY	LET.	WAS	DATE	BY	MATERIAL	DRAWN	CHK	APVD	SCALE	DATE DRAWN
				D	TERM # 5 & 6 EON 23958	1/25/89	JLP	FINISH	LIZ	888		1:1	9/8/87
				C1	PUT ON CAD	1/5/89	DPS						DATE BLUEPRINTED
				C	REVISED DMS/EON 23947	1/5/89	DPS	TOLERANCES					
					ISSUED	5/3/88	AF	DECIMAL ± ANGLE ±					
<p>Cole Hersee Co. 20 OLD COLONY AVENUE, SOUTH BOSTON, MA, U.S.A. 02127</p>													
<p>SWITCH TOGGLE S.P.S.T.</p>													59024-33

59024-35




MM	IN
0.96	0.038
1.82	0.072
2.51	0.099
2.56	0.101
3.97	0.156
5.02	0.198
5.13	0.202
6.35	0.250
8.63	0.340
8.76	0.345
10.31	0.406
13.30	0.524
13.46	0.530
19.05	0.750
20.70	0.815
20.83	0.820
33.52	1.320
39.14	1.541
41.40	1.630
41.65	1.640
44.62	1.756



98164 FACE NUT



TOP VIEW OF TOGGLE




- NOTES:
1. SILVER CONTACTS
  2. 25 AMPS @ 12VDC LAMP LOAD
  3. ALL STEEL PARTS PLATED
  4. FACE NUT ASSEMBLED
  5. PHENOLIC CONTACT PINS

METRIC

DO NOT SCALE  
CAD GENERATED

LET.	WAS	DATE	BY	LET.	WAS	DATE	BY	MATERIAL	DRAWN	CHK	APVD	SCALE	DATE DRAWN
									LIZ	<i>[Signature]</i>		1:1	9/8/87
								FINISH					DATE BLUEPRINTED
				C1	PUT ON CAD	1/5/89	DPS						
				C	REVISED DMS/EON 23947	1/5/89	DPS						
					ISSUED	5/3/88	AF	TOLERANCES DECIMAL ± ANGLE ±					
<p>Cole Hersee Co. 20 OLD COLONY AVENUE, SOUTH BOSTON, MA, U.S.A. 02127</p>													
<p>SWITCH TOGGLE D.P.S.T.</p>													59024-35

MM	IN
0.96	0.038
1.82	0.072
2.51	0.099
2.56	0.101
3.97	0.156
5.02	0.198
5.13	0.202
6.35	0.250
8.63	0.340
8.76	0.345
10.31	0.406
13.30	0.524
13.46	0.530
19.05	0.750
20.70	0.815
20.83	0.820
33.52	1.320
39.14	1.541
41.40	1.630
41.65	1.640
44.62	1.756



98164 FACE NUT



TOP VIEW OF TOGGLE

TOGGLE, PLASTIC, BLACK


FACE NUT, BLACK, ALUM., NOTE 4

BUSHING, 15/32, BLACK

INK STAMP PART NO & DATE CODE

MALE BLADE TERMINAL, TIN PLATED, 6 REQ'D



182 X 0.96 DEEP KEYWAY



"MOM ON"  
2 & 3  
5 & 6

"ON"  
2 & 3  
4 & 5

"MOM ON"  
1 & 2  
4 & 5



- NOTES:
1. SILVERED CONTACTS
  2. 25 AMPS @ 12VDC LAMP LOAD
  3. ALL STEEL PARTS PLATED
  4. FACE NUT ASSEMBLED
  5. PHENOLIC CONTACT PINS

METRIC

DO NOT SCALE  
CAD GENERATED

LET.	WAS	DATE	BY	LET.	WAS	DATE	BY	MATERIAL	DRAWN	CHK	APVD	SCALE	DATE DRAWN
									LIZ			1:1	9/8/87
								FINISH					DATE BLUEPRINTED
				C1	PUT ON CAD	1/5/89	DPS						
				C	REVISED DMS/EON 23947	1/5/89	DPS	TOLERANCES					
					ISSUED	5/3/88	AF	DECIMAL ± ANGLE ±					



SWITCH TOGGLE D.P.

59024-38