


REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	11/19/03	DD
"A"	WIRE DIA WAS 0.020"±0.001", WIRE LENGTH WAS 1.125" NOM	11/19/03	DD

RESISTANCE @ +25°C = 5,000 Ω ± 10%
RESISTANCE/TEMPERATURE CURVE = "F"
TEMPERATURE COEFFICIENT @ +25°C = −3.86%/°C NOMINAL
BETA "β" (0 TO +50°C) = 3,419°K NOMINAL
DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)
THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (WELL STIRRED OIL)
MAXIMUM TEMPERATURE RATING = +300°C

SCALE NONE

DRAWN BY
DAN DANKERT

DATE 06/19/97

REV. "A"

LAYER 0 OF 1

© COPYRIGHT

U.S. SENSOR CORP.

714-639-1000 www.ussensor.com

NTC THERMISTOR

P/N 502FG1K