




RESISTANCE @ +25°C = 10,000 Ω ± 1%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 MAXIMUM TEMPERATURE RATING = +105°C

MOUNTING-HOLE DIAMETER = 0.145" NOMINAL
 MOUNTING-HOLE STUD-SIZE = #6

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	09/03/03	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com THERMISTOR PROBE P/N USP4261
DRAWN BY DAN DANKERT	
DATE 09/03/03	
REV. NONE	
LAYER 0 OF 2	