


## High Voltage, High Gain BIMOSFET™ Monolithic Bipolar MOS Transistor

## IXBA16N170AHV IXBT16N170AHV

 $V_{CES} = 1700V$   $I_{CES} = 16A$ 

 $V_{CE(sat)} \le 6.0V$ 





Symbol	Test Conditions	Maximur	laximum Ratings		
V <sub>CES</sub>	T <sub>c</sub> = 25°C to 150°C	1700	V		
V <sub>CGR</sub>	$T_J = 25^{\circ}C$ to 150°C, $R_{GE} = 1M\Omega$	1700	V		
V <sub>GES</sub>	Continuous	± 20	V		
V <sub>GEM</sub>	Transient	± 30	V		
I <sub>C25</sub> I <sub>C90</sub> I <sub>CM</sub>	$T_{c} = 25^{\circ}C$ $T_{c} = 90^{\circ}C$ $T_{c} = 25^{\circ}C, 1ms$	16 10 40	A A A		
SSOA (RBSOA)	$V_{GE} = 15V$ , $T_{VJ} = 125^{\circ}C$ , $R_{G} = 33\Omega$ Clamped Inductive Load	I <sub>CM</sub> = 40 1350	A V		
t <sub>sc</sub> (SCSOA)	$V_{GE} = 15V$ , $V_{CE} = 1200V$ , $T_{J} = 125^{\circ}C$ $R_{G} = 33\Omega$ , Non Repetitive	10	μs		
P <sub>c</sub>	T <sub>c</sub> = 25°C	150	W		
T <sub>J</sub>		-55 +150	°C		
$T_{JM}$		150	°C		
T <sub>stg</sub>		-55 +150	°C		
T <sub>L</sub> T <sub>SOLD</sub>	Maximum Lead Temperature for Solderin Plastic Body for 10s	g 300 260	O°		
F <sub>c</sub>	Mounting Force (TO-263)	1065 / 2214.6	N/lb		
Weight	TO-263 TO-268	2.5 4.0	g 9		

10-200			7.0			
Symbol Test Conditions		Characteristic Values				
$(T_J = 25^{\circ}C$	Unless Otherwise Specified)	Min.	Тур.	Max.		
BV <sub>CES</sub>	$I_{\rm C} = 250 \mu A, V_{\rm GE} = 0 V$	1700			V	
V <sub>GE(th)</sub>	$I_{\rm C}=250\mu A,\ V_{\rm CE}=V_{\rm GE}$	2.5		5.5	V	
I <sub>CES</sub>	$V_{CE} = 0.8 \bullet V_{CES}, V_{GE} = 0V$	T <sub>J</sub> = 125°C		50 1.5	μA mA	
I <sub>GES</sub>	$V_{CE} = 0V, V_{GE} = \pm 20V$			±100	nA	
V <sub>CE(sat)</sub>	$I_{\rm C} = 10A, V_{\rm GE} = 15V, \text{ Note 1}$			6.0	V	
		$T_J = 125^{\circ}C$	5.0		V	





G = Gate C = Collector E = Emitter Tab = Collector

## **Features**

- High Voltage Package
- High Blocking Voltage
- Anti-Parallel Diode
- Low Conduction Losses

## **Advantages**

- Low Gate Drive Requirement
- High Power Density

## Applications:

- Switch-Mode and Resonant-Mode Power Supplies
- Uninterruptible Power Supplies (UPS)
- Laser Generators
- Capacitor Discharge Circuits
- AC Switches



-	Symbol Test Conditions Characteristic Values		alues			
$(T_{J} = 25)$	°C U	nless Otherwise Specified)	Min.	Тур.	Max.	
<b>g</b> <sub>fs</sub>		$I_{\rm C} = 10A, V_{\rm CE} = 10V, \text{ Note 1}$	8.0	12.5		S
C <sub>ies</sub>	)			1400		pF
C <sub>oes</sub>	}	$V_{CE} = 25V, V_{GE} = 0V, f = 1MHz$		90		pF
C <sub>res</sub>	J			31		pF
$Q_{g(on)}$	)			65		nC
$\mathbf{Q}_{ge}$	}	$I_{\rm C} = 10$ A, $V_{\rm GE} = 15$ V, $V_{\rm CE} = 0.5 \bullet V_{\rm CES}$		13		nC
Q <sub>gc</sub>	J			22		nC
t <sub>d(on)</sub>	)	Inductive load, T <sub>.</sub> = 25°C		15		ns
t <sub>ri</sub>		$I_{\rm C} = 10A$ , $V_{\rm GE} = 15V$		25		ns
$\mathbf{t}_{d(off)}$	}	$V_{CE} = 0.8 \cdot V_{CES}, R_{G} = 10\Omega$		160	250	ns
t <sub>fi</sub>		Note 2		50	100	ns
E <sub>off</sub>	J	Note 2		1.2	2.5	mJ
$\mathbf{t}_{d(on)}$	)			15		ns
t <sub>ri</sub>		Inductive load, T <sub>J</sub> = 125°C		28		ns
E <sub>on</sub>	- (	$I_{\rm C} = 10A, \ V_{\rm GE} = 15V$		2.0		mJ
$\mathbf{t}_{d(off)}$		$V_{CE} = 0.8 \bullet V_{CES}, R_{G} = 10\Omega$		220		ns
t <sub>fi</sub>		Note 2		150		ns
E <sub>off</sub>	)			2.6		mJ
$R_{\text{thJC}}$					0.83	°C/W

# TO-263HV Outline PIN: 1 - Gate 2 - Emitter 3 - Collector

SYM	INCH	HES	MILLIMETER	
SIM	MIN	MAX	MIN	MAX
Α	.170	.185	4.30	4.70
A1	.000	.008	0.00	0.20
A2	.091	.098	2.30	2.50
Ь	.028	.035	0.70	0.90
b2	.046	.054	1.18	1.38
С	.018	.024	0.45	0.60
C2	.049	.055	1.25	1.40
D	.354	.370	9.00	9.40
D1	.311	.327	7.90	8.30
E	.386	.402	9.80	10.20
E1	.307	.323	7.80	8.20
e1	.200	BSC	5.08 BSC	
(e2)	.163	.174	4.13	4.43
H	.591	.614	15.00	15.60
L	.079	.102	2.00	2.60
L1	.039	.055	1.00	1.40
L3	.010	BSC	0.254	BSC
(L4)	.071	.087	1.80	2.20

## **Reverse Diode**

•			Values Max.		
V <sub>F</sub>		$I_{F} = 10A, V_{GE} = 0V$		5.0	V
t <sub>rr</sub>	)	$I_F = 10A, V_{GE} = 0V, -di_F/dt = 50A/\mu s$	360		ns
I <sub>RM</sub>	Ĵ	$V_R = 100V, V_{GE} = 0V$	10		Α

### Notes:

- 1. Pulse test,  $t \le 300\mu s$ , duty cycle,  $d \le 2\%$ .
- 2. Switching times & energy losses may increase for higher  $V_{CE}$ (clamp),  $T_J$  or  $R_g$ .

## **ADVANCE TECHNICAL INFORMATION**

The product presented herein is under development. The Technical Specifications offered are derived from a subjective evaluation of the design, based upon prior knowledge and experience, and constitute a "considered reflection" of the anticipated result. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

## TO-268HV Outline PIN: 1 - Gate 2 - Emitter 3 - Collector INCHES MILLIMETER

SYM	INCH	HES .	MILLIN	METER	
STIVI	MIN	MAX	MIN	MAX	
А	.193	.201	4.90	5.10	
A1	.106	.114	2.70	2.90	
A2	.001	.010	0.02	0.25	
Ь	.045	.057	1.15	1.45	
С	.016	.026	0.40	0.65	
C2	.057	.063	1.45	1.60	
D	.543	.551	13.80	14.00	
D1	.465	.476	11.80	12.10	
D2	.295	.307	7.50	7.80	
D3	.114	.126	2.90	3.20	
E	.624	.632	15.85	16.05	
E1	.524	.535	13.30	13.60	
е	.215	BSC	5.45 BSC		
Н	.736	.752	18.70	19.10	
L	.067	.079	1.70	2.00	
L2	.039	.045	1.00	1.15	
L3	.010	BSC	0.25 BSC		
L4	.150	.161	3.80	4.10	

IXYS Reserves the Right to Change Limits, Test Conditions and Dimensions.

