



#	DESCRIPTION	PART #
A	2-POSITION	882-839-2
B	3-POSITION	882-839-3
C	4-POSITION	882-839-4
D	5-POSITION	882-839-5

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
◎		UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES		
◎		UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.		
◎		DENOTES CRITICAL CHARACTERISTICS.		
CPK		DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ST		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP		DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		

COPIES TO		MATERIAL SPEC		FINISH		SCALE		FULL	
LTR	DATE	REVISION	CHK	APD	DRW	OPL	DATE	DATE	DATE
1	9	18	COPPER C1100	TIN-PLATED	DATE	02/17/11	SCALE	FULL	
2	10	19			CHK		SUPER DR		
3	12	20			APPD		FINISH GOOD WT		
4	13	21			TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)				
5	14	23			DIMENSION	UP TO	OVER	UP TO	OVER
6	15	33			TOLERANCE	+0.05	±0.05	±0.15	±0.2
7	16	43			3RD ANGLE PROJECTION				
8	17	53			TITLE		BUS BAR FOR FLEX MEGA HOLDER		
LITTELFUSE		REVISION		DRWG. NO.					
DES. PLAINES, ILLINOIS 60016		B		882-839-0					