

## **PolarP™ Power MOSFET**

## IXTC36P15P IXTR36P15P

### (Electrically Isolated Tab)


P-Channel Enhancement Mode Avalanche Rated




Symbol	Test Conditions	Maximum Ratings		
V <sub>DSS</sub>	$T_{_{\rm J}} = 25^{\circ}\text{C to } 175^{\circ}\text{C}$	-150	V	
V <sub>DGR</sub>	$T_{_J} = 25^{\circ}C$ to 175°C, $R_{_{GS}} = 1M\Omega$	-150	V	
$\mathbf{V}_{GSS}$	Continuous	± 20	V	
V <sub>GSM</sub>	Transient	± 30	V	
I <sub>D25</sub>	T <sub>C</sub> = 25°C	- 22	A	
I <sub>DM</sub>	$T_{\rm C} = 25^{\circ}$ C, Pulse Width Limited by $T_{\rm JM}$	-100	Α	
I <sub>A</sub>	T <sub>C</sub> = 25°C	- 36	Α	
<b>E</b> <sub>AS</sub>	$T_{c} = 25^{\circ}C$	1.5	J	
dv/dt	$I_{_{S}} \le I_{_{DM}}, V_{_{DD}} \le V_{_{DSS}}, T_{_{J}} \le 175^{\circ}C$	10	V/ns	
P <sub>D</sub>	T <sub>C</sub> = 25°C	150	W	
T <sub>J</sub>		- 55 +175	°C	
T <sub>JM</sub>		175	°C	
T <sub>stg</sub>		- 55 +175	°C	
$T_L$	1.6mm (0.062 in.) from Case for 10s	300	°C	
T <sub>SOLD</sub>	Plastic Body for 10s	260	°C	
V <sub>ISOL</sub>	50/60 Hz, RMS, t = 1minute	2500	V~	
F <sub>c</sub>	Mounting Force (ISOPLUS220)	1165 / 2514.6	N/lb	
F <sub>c</sub>	Mounting Force (ISOPLUS247)	20120 / 4.527	N/lb	
Weight	ISOPLUS220 ISOPLUS247	2 5	g g	

SymbolTest ConditionsChara $(T_J = 25^{\circ}\text{C}, \text{Unless Otherwise Specified})$ Min.		cteristic	c Value Max.	-	
BV <sub>DSS</sub>	$V_{GS} = 0V$ , $I_D = -250\mu A$	-150			V
V <sub>GS(th)</sub>	$V_{DS} = V_{GS}$ , $I_D = -250\mu A$	- 3.0		- 5.0	V
I <sub>GSS</sub>	$V_{GS} = \pm 20V, V_{DS} = 0V$			±100	nA
I <sub>DSS</sub>	$V_{DS} = V_{DSS}, V_{GS} = 0V$ $T_{J} = 150^{\circ}C$			- 10 - 250	•
R <sub>DS(on)</sub>	$V_{GS} = -10V, I_{D} = -18A, Note 1$			120	mΩ

 $V_{DSS} = -150V$   $I_{D25} = -22A$   $R_{D25} \leq 120m\Omega$ 





G = Gate D = Drain S = Source

#### **Features**

- Silicon Chip on Direct-Copper Bond (DCB) Substrate
- Isolated Mounting Surface
- 2500V~ Electrical Isolation
- Avalanche Rated
- Extended FBSOA
- Fast Intrinsic Diode
- $^{ullet}$  Low  $R_{\scriptscriptstyle DS(ON)}$  and  $Q_{\scriptscriptstyle G}$

#### **Advantages**

- Easy to Mount
- Space Savings
- High Power Density

#### **Applications**

- High-Side Switching
- Push Pull Amplifiers
- DC Choppers
- Automatic Test Equipment
- Current Regulators
- Battery Charger Applications



Symbol	Test Conditions	Chara	cteristic	Values
$(T_{J} = 25^{\circ}C, V)$	Unless Otherwise Specified)	Min.	Тур.	Max.
g <sub>fs</sub>	$V_{DS} = -10V, I_{D} = -18A, \text{ Note } 1$	11	19	S
C <sub>iss</sub>			2950	pF
C <sub>oss</sub>	$V_{GS} = 0V, V_{DS} = -25V, f = 1MHz$		615	pF
C <sub>rss</sub>			115	pF
t <sub>d(on)</sub>	Resistive Switching Times		28	ns
t,	•		37	ns
t <sub>d(off)</sub>	$V_{GS} = -10V$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_{D} = -18A$ $R_{G} = 5\Omega$ (External)		45	ns
t,			14	ns
Q <sub>g(on)</sub>			55	nC
Q <sub>gs</sub>	$V_{GS} = -10V$ , $V_{DS} = 0.5 \cdot V_{DSS}$ , $I_{D} = -18A$		21	nC
$Q_{gd}$			20	nC
R <sub>thJC</sub>				1.00 °C/W
$\mathbf{R}_{\mathrm{thCS}}$			0.15	°C/W

#### Source-Drain Diode


SymbolTest ConditionsChar $(T_J = 25^{\circ}C, Unless Otherwise Specified)$ Mir			cteristic Values Typ.   Max.		
Is	$V_{GS} = 0V$		- 36	Α	
I <sub>SM</sub>	Repetitive, Pulse Width Limited by $T_{_{JM}}$		-100	Α	
V <sub>SD</sub>	$I_F = -18A, V_{GS} = 0V, \text{ Note 1}$		- 3.0	V	
t <sub>rr</sub> Q <sub>RM</sub>	$ \begin{cases} I_F = -25, -di/dt = -100A/\mu s \\ V_R = -100V, V_{GS} = 0V \end{cases} $	150 2.0		ns µC	

Note 1: Pulse test,  $t \le 300\mu s$ , duty cycle,  $d \le 2\%$ .

#### PRELIMINARY TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from data gathered during objective characterizations of preliminary engineering lots; but also may yet contain some information supplied during a pre-production design evaluation. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

# ISOPLUS220™ Outline




Note: Bottom heatsink (Pin 4) is electrically isolated from Pin 1,2, or 3.

CVM	INCHES		MILLIMETERS		
SYM	MIN	MAX	MIN	MAX	
A	.157	197	4.00	5.00	
A2	.098	.118	2.50	3.00	
ь	.035	.051	0.90	1.30	
ь2	.049	.065	1.25	1.65	
b4	.093	.100	2.35	2.55	
С	.028	.039	0.70	1.00	
D	.591	.630	15.00	16.00	
D1	.472	.512	12.00	13.00	
Ε	.394	.433	10.00	11.00	
E1	.295	.335	7.50	8.51	
е	.1DO BASIC		2.55 BASIC		
L	.512	.571	13.00	14.50	
L1	.118	.138	3.00	3.50	
L.			42.5°	47.5'	

Ref: IXYS CO 0177 R0





Terminals: 1 - Gate

2 - Drain (Collector)

3 - Source (Emitter) 4 - Drain (Collector)

Dim.	Millimeter Inches		nes	
	Min.	Max.	Min.	Max.
Α	4.83	5.21	.190	.205
Α,	2.29	2.54	.090	.100
A <sub>2</sub>	1.91	2.16	.075	.085
b	1.14	1.40	.045	.055
b <sub>1</sub>	1.91	2.13	.075	.084
b <sub>2</sub>	2.92	3.12	.115	.123
С	0.61	0.80	.024	.031
D	20.80	21.34	.819	.840
Е	15.75	16.13	.620	.635
е	5.45 BSC		.215 BSC	
L	19.81	20.32	.780	.800
L1	3.81	4.32	.150	.170
Q	5.59	6.20	.220	0.244
R	4.32	4.83	.170	.190

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

