

SLC CLASS G FUSES

480/600 V ac • Time-Delay • 1/2-60 A





Specifications

Voltage Ratings 600 V ac (1/2 - 20 A)

480 V ac (25 – 60 A) 170 V dc (1/2 – 60 A)

Interrupting Ratings AC: 100 kA rms symmetrical

DC: 10 kA

Ampere Range 1/2 - 60 A

Approvals Standard 248-5, Class G

UL Listed (File: E81895) CSA Certified (File: LR29862) Federal Specification WF-1814

(QPL-W-F-1814)

Environmental RoHS Compliant

Description

Littelfuse SLC fuses provide cost effective branch circuit protection. Fuse length varies to prevent over-fusing. Compact Class G fuses were the first fuse series to approach midget fuse dimensions and meet NEC® requirements for branch-circuit protection.

Features/Benefits

- Branch circuit rated
- Current-limiting
- 100 kA interrupting rating
- 600 V ac rated 1/2-20 A

Applications

• Branch circuit protection

Web Resources


Download TC Curves, CAD drawings and other technical information: **littelfuse.com/slc**

Recommended Fuse Holders

LFG60 Series (½-20 A) LFG48 Series (25-60 A)

Ordering Information


Part Numbering System



SERIES	AMP	PACKAGE QUANTITY	CATALOG NUMBER	ORDERING NUMBER
SLC	2	10	SLC002	OSLC002.T

Dimensions

Ferrule Version



AMP	DIMENSIONS INCHES (mm)				
Alvii	Α	В	С	D	
$^{1}/_{2}-15$	1 5/16 (33.3)	3/8 (9.5)	3/8 (9.5)	13/32 (10.3)	
20	1 13/32 (35.7)	3/8 (9.5)	3/8 (9.5)	13/32 (10.3)	
25, 30	1 5/8 (41.3)	3/8 (9.5)	3/8 (9.5)	13/32 (10.3)	
35 - 60	2 1/4 (57.2)	3/8 (9.5)	1/2 (12.7)	13/32 (10.3)	

Disclaimer Notice – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/product-disclaimer.