


458 Series Fuse



Agency Approvals			
Agency	Agency File Number	Ampere Range	
c FL ° us	E10480	1A-10A	

Opening Time

4 hours, Minimum

5 seconds, Maximum

Description

The 458 Series Nano^{2®} Fuse is an ultra-small, square surface mount fuse designed to support a variety of space constrained overcurrent protection applications. Offering a 1206 size footprint, it is the smallest wire-in-air type surface mount fuse offered by Littelfuse.

Features

- Surface Mount Fuse
- Fully compatible with lead free soldering profiles • RoHS Compliant and
- Available in ratings of 1 to 10 Amperes
- Recognized to UL/CSA/ NMX 248-1 and UL/CSA/ NMX 248-14

Applications

Notebook PC

Halogen-Free

- LCD backlight inverter
- LCD Panel
- DC/DC converter
- Battery Pack
- Car Navigation System
- Network Equipment
- **Telecom Equipment** •
- Electronic Signage •
- Portable Consumer • Electronics

Additional Information





Resources



Samples

Electrical Specifications by Item

Electrical Characteristics for Series

% of Ampere Rating

100%

250%

Ampere Rating (A)	Amp Code	Marking	Max Voltage Rating (V)	Interrupting Rating	Nominal Cold Resistance (Ohms)	Nominal Melting I²t (A²sec)	Agency Approvals
1.25	1.25	1.25		0.125	.313	X	
1.5	01.5	1.5		0.099	.548	Х	
1.6	01.6	1.6		0.092	.562	X	
2	002.	2		0.0695	.952	Х	
2.5	02.5	2.5	50A @ 48VAC	0.06	1.408	Х	
3	003.	3	0.049	2.289	Х		
3.15	3.15	3.15	0.045	2.457	X		
3.5	03.5	3.5	_		0.0375	4.00	x
4	004.	4	-		0.032	4.832	x
5	005.	5		50A @ 75VDC	0.027	7.938	x
6.3	06.3	6.3		50A @ 32VAC	0.0192	14.37	X
7	007.	7	63V	50A @ 63VDC	0.0175	20.48	х
8	008.	8		50A @ 83VDC 50A @ 32VAC	0.0058	13.448	X
10.0	010.	10		SUA @ 32VAC	0.00465	15.0	x


Notes:

1. I²t values stated for 8 msec opening time

Cold resistance measured at less than 10% of rated current at 25°C.
Agency Approval Table Key: X=Approved or Certified, P=Pending and Blank=Not Approved
Have special electrical characteristic needs? Contact Littelfuse to learn more about application specific options.




Temperature Re-rating Curve



Note:


 $\textbf{1.} \ensuremath{\text{Rerating depicted in this curve is in addition to the standard rerating of 25\% for continuous operation.}$

Average Time Current Curves



Soldering Parameters

Reflow Condition		Pb – Free assembly	
Pre Heat	- Temperature Min (T _{s(min)})	150°C	
	- Temperature Max (T _{s(max)})	200°C	
	- Time (Min to Max) (t _s)	60 – 180 secs	
Average ramp up rate (Liquidus Temp (T_L) to peak		5°C/second max	
T _{S(max)} to T _L - Ramp-up Rate		5°C/second max	
Reflow	- Temperature (T_L) (Liquidus)	217°C	
	- Temperature (t _L)	60 – 150 seconds	
Peak Temperature (T _P)		260 ^{+0/-5} °C	
Time within 5°C of actual peak Temperature (t _p)		20 – 40 seconds	
Ramp-down Rate		5°C/second max	
Time 25°C to peak Temperature (T _P)		8 minutes Max.	
Do not exceed		260°C	





Product Characteristics

Dimensions

Materials	Body: Ceramic Cap: Gold Plated Brass	
Product Marking	Body: Current Rating (Refer to Electrical Characteristic table)	
Insulation Resistance (after Opening)	MIL-STD-202, Method 302, Test Condition A (10,000 ohms, Minimum)	
Solderability	MIL-STD-202, Method 208	
Resistance to Soldering Heat	MIL-STD-202, Method 210, Test Condition B (10 sec at 260°C)	
Moisture Sensitivity Level	Level 1 J-STD-020	

3.175 (.125‴)

7

3.65 (.143")

2.05 (.081″)

1

Recommended Pad Layout

1.28

(.050")


1.185

(.047")

0.813 (.032")

Operating Temperature	–55°C to 125°C with proper derating	
Thermal Shock	MIL-STD-202, Method 107, Test Condition B (5 cycles -65°C to +125°C)	
Vibration	MIL-STD-202, Method 201(10-55 Hz)	
Moisture Resistance	MIL-STD-202, Method 106, High Humidity (90- 98%RH), Heat (65°C)	
Salt Spray	MIL-STD-202, Method 101, Test Condition B	
Shock	MIL-STD-202, Method 213, Test Condition I (100 G's peak for 6 milliseconds)	

Part Numbering System



1.5 amp product is 0458 D R (1 amp product shown above).

Packaging			
Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
8mm Tape and Beel	EIA-BS 481-1	1500	DB

1.575 (.062″)

1.575 (.062″)

ţ

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall be deemed void for any claims or damages arising out of products used in applications not expressly is there doe by Littelfuse accumentation. Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.