## TVS Diode Arrays (SPA® Diodes) Datasheet

# SC1210-01ETG

**Bidirectional Discrete TVS Diode, General Purpose Surge Protection** 





Note: This package image is for example and reference only. for detail package drawing, please refer to the package section in this datasheet.

## Pinout



## **Functional Block Diagram**



## Description

The SC1210-01ETG bidirectional TVS is fabricated in a proprietary silicon avalanche technology. These diodes provide a high ESD (electrostatic discharge) protection level for electronic equipment. The SC1210-01ETG TVS can safely absorb repetitive ESD strikes of  $\pm 30$  kV (contact and air discharge as defined in IEC 61000-4-2) without any performance degradation. Additional, each TVS can safely dissipate a 15A 8/20us surge event as defined in IEC 61000-4-5 2<sup>nd</sup> edition.

### **Features**

- ESD, IEC 61000-4-2, ±30kV contact, ±30kV air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Lightning, 15A (8/20µs as defined in IEC 61000-4-5 2<sup>nd</sup> edition)
- Low leakage current of 0.02µA (TYP) at 5V
- Halogen free, lead free and RoHS compliant
- Moisture Sensitivity Level (MSL -1)

## Applications

- Switches / Buttons
- Test Equipment /
  - Instrumentation
- Point-of-Sale Terminals
- Medical Equipment
- Notebooks / Desktops / Servers
- Computer Peripherals
- Battery

#### Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.



Bidirectional Discrete TVS Diode, General Purpose Surge Protection

## **Absolute Maximum Ratings**

Symbol	Parameter	Value	Units
I <sub>PP</sub>	Peak Current (t <sub>p</sub> =8/20µs)	15	А
T <sub>op</sub>	Operating Temperature	-40 to 125	°C
T	Storage Temperature	-55 to 150	°C

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

## **Electrical Characteristics (T<sub>OP</sub>=25°C)**


Parameter	Symbol	Test Conditions	Min	Тур	Мах	Units
Reverse Standoff Voltage	V <sub>RWM</sub>	I <sub>R</sub> =1µA			5	V
Breakdown Voltage	V <sub>BR</sub>	I <sub>R</sub> =1mA	5.2	5.5		V
Reverse Leakage Current	I	V <sub>R</sub> =5V		0.02	0.1	μA
Clamp Voltage <sup>1</sup>	V <sub>c</sub>	I <sub>PP</sub> =15Α, t <sub>p</sub> =8/20μs		11		V
Dynamic Resistance <sup>2</sup>	R <sub>DYN</sub>	TLP, t <sub>p</sub> =100ns		0.11		Ω
ESD Withstand Voltage <sup>1</sup>	V <sub>ESD</sub>	IEC 61000-4-2 (Contact Discharge)	±30			kV
		IEC 61000-4-2 (Air Discharge)	±30			kV
Diode Capacitance <sup>1</sup>	C <sub>IO-GND</sub>	Reverse Bias=0V, f=1MHz		26		pF

### Note:

1. Parameter is guaranteed by design and/or component characterization.

2.Transmission Line Pulse (TLP) with 100ns width, 0.2ns rise time, and average window t1=70ns to t2= 90ns


### 8/20µs Pulse Waveform






## TVS Diode Arrays (SPA® Diodes) Datasheet

## **SC1210-01ETG** Bidirectional Discrete TVS Diode, General Purpose Surge Protection



### Capacitance vs Reverse Bias

Clamping Voltage vs I<sub>PP</sub>



**Negative Transmission Line Pulsing (TLP) Plot** 

0

-2

-4

-6

-8

-10

-12

-14

-16

-18

-20

-22


-24

-12 -11 -10

-9 -8 -7 -6 -5 -4 -3 -2 -1 0

TLP Current (A)

### Positive Transmission Line Pulsing (TLP) Plot




IEC 61000-4-2 +8 kV Contact ESD Clamping Voltage



IEC 61000-4-2 -8 kV Contact ESD Clamping Voltage

TLP Voltage (V)






## TVS Diode Arrays (SPA® Diodes) Datasheet

# SC1210-01ETG

Bidirectional Discrete TVS Diode, General Purpose Surge Protection

## **Soldering Perameters**

Reflow Condition		Pb – Free assembly	
Pre Heat	- Temperature Min (T <sub>s(min)</sub> )	150°C	
	- Temperature Max (T <sub>s(max)</sub> )	200°C	
	- Time (min to max) (t <sub>s</sub> )	60 - 180 secs	
Average ra (T <sub>L</sub> ) to pea	amp up rate (Liquidus) Temp k	3°C/second max	
T <sub>S(max)</sub> to T <sub>L</sub>	- Ramp-up Rate	3°C/second max	
Reflow	- Temperature (T <sub>L</sub> ) (Liquidus)	217°C	
	- Temperature (t <sub>L</sub> )	60 – 150 seconds	
Peak Temp	erature (T <sub>P</sub> )	260 <sup>+0/-5</sup> °C	
Time with Temperatu	in 5°C of actual peak ıre (t <sub>p</sub> )	20 – 40 seconds	
Ramp-down Rate		6°C/second max	
Time 25°C to peak Temperature (T <sub>P</sub> )		8 minutes Max.	
Do not exceed		260°C	




## **Product Characteristics**

Lead Plating	Matte Tin
Lead material	Copper Alloy
Substrate Material	Silicon
Body Material	Molded Compound
Flammability	UL Recognized compound meeting flammability rating V-0


# Ordering Information

Part Number	Package	Min. Order Qty.
SC1210-01ETG	SOD882	10,000

## **Part Marking System**





## Part Numbering System



Bidirectional Discrete TVS Diode, General Purpose Surge Protection

## Package Dimensions - SOD882











Millimeters Inches Symbol Min Max Min Max Typ Тур 0.40 0.50 0.55 0.016 0.020 0.022 А A1 0.00 0.02 0.05 0.000 0.001 0.002 L1 0.20 0.25 0.30 0.008 0.010 0.012 12 0.45 0.50 0.55 0.018 0.020 0.022 0.041 D 0.95 1.00 1.05 0.037 0.039 Е 0.55 0.60 0.65 0.022 0.024 0.026 0.65 BSC 0.026 BSC е

SOD882

## Embossed Carrier Tape & Reel Specification - SOD882





Product Disclaimer: Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. "Littelfuse" includes Littelfuse, Inc., and all of its affiliate entities. <u>http://www.littelfuse.com/disclaimer-electronics</u>.

