


# SP03-6 Series 6V 150A Diode Array











## **Description**

This new broadband protection component from Littelfuse provides overvoltage protection for applications such as 10/100/1000 BaseT Ethernet, T3/E3 DS3 interfaces, ADSL2+, and VDSL2+. This new protector combines the TVS diode element with a diode rectifier bridge to provide both longitudinal and differential protection in one package. This innovative design results in a capacitive loading characteristic that is log-linear with respect to the signal voltage across the device. This reduces intermodulation (IM) distortion caused by a typical solid-state protection solution.


#### **Agency Approvals**

Agency	Agency File Number
<b>7U</b> °	E128662

#### **Features**

- · RoHS-compliant and lead-
- SOIC-8 surface mount package (JEDEC MS-012)
- · Low insertion loss, loglinear capacitance
- Combined longitudinal and differential protection
- Clamping speed of nanoseconds
- UL Recognized compound meeting flammability rating V-0
- Lightning, 150A (8/20 as defined in IEC 61000-4-5 2nd Edition)
- Low clamping voltage

#### **Pinout**




SOIC-8 (Top View)

## **Applications**


- T1/E1 Line cards
- T3/E3 and DS3 Interfaces
- STS-1 Interfaces

### • 10/100/1000 BaseT Ethernet

#### **Functional Block Diagram**



## **Application Example**



This schematic shows a high-speed data interface protection solution. The SP03-6 provides both metallic (differential) and longitudinal (common mode) protection from lightning induced surge events. Its surge rating is compatible with the intra-building surge requirements of Telcordia's GR-1089-CORE, and the Basic Level Recommendations of ITU K.20 and K.21. This component protects against both positive and negative induced surge events. The TeleLink fuse provides overcurrent protection for the long term 50/60 Hz power fault events.

## **Additional Information**







Samples

Life Support Note:

#### Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.



## **Absolute Maximum Ratings**


Parameter	Rating	Units
Peak Pulse Current (8/20µs)	150	А
Peak Pulse Power (8/20µs)	2800	W
IEC 61000-4-2, Contact Discharge, (Level 4)	30	kV
IEC 61000-4-2, Air Discharge, (Level 4)	30	kV
IEC 61000-4-5, 2nd Edition (8/20)	100	А
Telcordia GR 1089 (Intra-Building) (2/10µs)	150	А
ITU K.20 (5/310μs)	40	А

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

# **Electrical Characteristics (T<sub>OP</sub> = 25°C)**

Parameter	Symbol	Test Conditions	Min	Тур	Max	Units
Reverse Stand-Off Voltage	V <sub>RWM</sub>	-	-	-	6	V
Reverse Breakdown Voltage	V <sub>BR</sub>	I <sub>T</sub> = 1mA	6.8	-	-	V
Reverse Leakage Current	I <sub>R</sub>	V <sub>RWM</sub> = 6V, T= 25°C	-	-	25	μА
Clamping Voltage, Line-Ground	V <sub>c</sub>	$I_{pp} = 50A, t_p = 8/20 \mu s$	-	-	15	V
Clamping Voltage, Line-Ground	V <sub>C</sub>	I <sub>pp</sub> = 100A, t <sub>p</sub> =8/20 μs	-	-	20	V
lunction Consistence	C <sub>j</sub> (Line-Ground)	Between I/O Pins and Ground $V_R=0V$ , f= 1MHz	-	16	25	pF
Junction Capacitance	C <sub>j</sub> (Line-Line)	Between I/O Pins V <sub>R</sub> =0V, f= 1MHz	-	8	12	pF

Figure 1: Non-repetitive Peak Pulse Current vs. Pulse Time



**Figure 2: Current Derating Curve** 






Figure 3: Pulse Waveform




Figure 4: Clamping Voltage vs. Peak Pulse Current




Figure 5: Capacitance vs. Reverse Voltage






Figure 6: Forward Voltage vs. Forward Current




## **Soldering Parameters**

Reflow Condition		Pb – Free assembly
	- Temperature Min (T <sub>s(min)</sub> )	150°C
Pre Heat	- Temperature Max (T <sub>s(max)</sub> )	200°C
	-Time (min to max) (t <sub>s</sub> )	60 – 180 secs
Average ramp up rate (Liquidus) Temp (T <sub>L</sub> ) to peak		3°C/second max
T <sub>S(max)</sub> to T <sub>L</sub> - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T <sub>L</sub> ) (Liquidus)	217°C
Renow	- Temperature (t <sub>L</sub> )	60 - 150 seconds
Peak Temperature (T <sub>p</sub> )		260 <sup>+0/-5</sup> °C
Time within 5°C of actual peak Temperature (tp)		20 - 40 seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T <sub>p</sub> )		8 minutes Max.
Do not exceed		260°C






## Package Dimensions — Mechanical Drawings and Recommended Solder Pad Outline




Package		SC	DIC	
Pins	8			
JEDEC	MS-012			
	Millin	netres	Inc	hes
	Min	Max	Min	Max
Α	1.35	1.75	0.053	0.069
A1	0.10	0.25	0.004	0.010
A2	1.25	1.65	0.049	0.065
В	0.31	0.51	0.012	0.020
С	0.17	0.25	0.007	0.010
D	4.80	5.00	0.189	0.197
E	5.80	6.20	0.228	0.244
E1	3.80	4.00	0.150	0.157
е	1.27	BSC	0.050	BSC
L	0.40	1.27	0.016	0.050

## Embossed Carrier Tape & Reel Specification — SOIC Package



	Milli	metres	In	ches
	Min	Max	Min	Max
E	1.65	1.85	0.065	0.073
F	5.4	5.6	0.213	0.22
P2	1.95	2.05	0.077	0.081
D	1.5	1.6	0.059	0.063
D1	1.50	) Min	0.05	9 Min
P0	3.9	4.1	0.154	0.161
10P0	40.0	± 0.20	1.574	± 0.008
W	11.9	12.1	0.468	0.476
Р	7.9	8.1	0.311	0.319
A0	6.3	6.5	0.248	0.256
В0	5.1	5.3	0.2	0.209
K0	2	2.2	0.079	0.087
t	0.30	± 0.05	0.012	± 0.002

## **Part Numbering System**



# **Product Characteristics**

F SP03-6 CYYWW C= Location	Part Marking System	
PIN 1————————————————————————————————————		

## **Ordering Information**

Part Number	Package	Marking	Min. Order Qty.
SP03-6BTG	SOIC Tape & Reel	SP03-6	2500

Lead Plating	Matte Tin
Lead Material	Copper Alloy
Lead Coplanarity	0.003 inches (0.08 mm)
Substrate Material	Silicon
<b>Body Material</b>	Molded
Flammability	UL Recognized compound meeting flammability rating V-0

- All dimensions are in millimeters
   Dimensions include solder plating.
   Dimensions are exclusive of mold flash & metal burr.
- Blo is facing up for mold and facing down for trim/form, i.e. reverse trim/form.
   Package surface matte finish VDI 11-13.

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at http://www.littelfuse.com/disclaimer-electronics.