


PGR-6800 SERIES

Pump Protection Relay





Simplified Circuit Diagram



Description

The PGR-6800 Pump Protection Relay provides protection for pumps with three-phase motors up to 1,000 Vac. No current transformers are required for currents up to 91 A. The protective functions include overload, phase unbalance, phase loss, phase sequence and undercurrent. The PGR-6800 Pump Protection Relay is ideally suited for applications where operating without load can induce failure. Motor current is monitored and an undercurrent trip occurs when the current drops below a preset level. No additional level detectors are required.

Features & Benefits

BENEFITS
No current transformers required for currents up to 91 $\mbox{\ensuremath{A}}$
Adjustable overload trip class setting from 5 to 15 for use with a wide variety of pumps
Form A and Form B ground-fault output contacts for operation of separate annunciation and trip circuits
Cause-of-trip indication and reset button
Prevents insulation failures and fires; extends motor life
Detects unhealthy supply conditions
Prevents overheating due to unbalanced phases
Detects low level or no-load conditions

Accessories





PGB-6800 Remote Indication and Reset Assembly

Optional remote indication of overload, undercurrent, phase unbalance, phase loss, and phase sequence. Remote reset included.

Ordering Information

ORDERING NUMBER	CONTROL POWER	FULL-LOAD CURRENT
PGR-6801-24	24 Vdc	7-19.6 A
PGR-6801-120	120 Vac	7-19.6 A
PGR-6801-240	240 Vac	7-19.6 A
PGR-6802-24	24 Vdc	19-44.2 A
PGR-6802-120	120 Vac	19-44.2 A
PGR-6802-240	240 Vac	19-44.2 A
PGR-6803-24	24 Vdc	40-90.4 A
PGR-6803-120	120 Vac	40-90.4 A
PGR-6803-240	240 Vac	40-90.4 A

ACCESSORIES	REQUIREMENT
PGB-6800	Optional

Specifications

Mounting

Protective Functions Overload (49, 51) Unbalance (current) (46) (IEEE Device Numbers) Phase sequence (46) Phase loss (current) (46) Undercurrent (37) Input Voltage See ordering information Frequency 50, 60 Hz **Dimensions H** 83 mm (3.3"); **W** 78 mm (3.1"); **D** 99 mm (3.9") **Test Button** Standard feature **Reset Button** Standard feature **Output Contacts** Isolated form A and Form B **Approvals** UL Listed (E343314) Warranty 5 years

DIN