

PLMU11

Voltage Monitor








8-PIN

Wiring Diagram



F = Fuses

 $\emptyset A = Phase A = L1$

 $\emptyset B = Phase B = L2$ $\emptyset C = Phase C = L3$

NO = Normally Open NC = Normally Closed

2A fast acting fuses recommended for safety (not required).

Relay contacts are isolated

Description

The PLMU11 continuously measures the voltage of each of the three phases to provide protection for 3-phase motors and sensitive loads. Its microcontroller senses under and overvoltage, voltage unbalance, phase loss, and phase reversal. Protection is provided even when regenerated voltages are present. Universal voltage operation and standard base connection allows the PLMU11 to replace hundreds of competitive part numbers.

Operation

Upon application of power, a 0.6s random start delay begins and the PLMU11 measures the voltage levels and line frequency and selects the voltage range. The output relay is energized and the LED glows green when all voltages are acceptable and the phase sequence is correct. LED flashes green during trip delay, glows red when output de-energizes. Undervoltage, overvoltage, and voltage unbalance must be sensed for continuous trip delay before the relay de-energizes. Re-energization is automatic upon fault correction. The output relay will not energize if a fault condition is sensed as 3-phase input voltage is applied. The LED alternately flashes red/green when phase reversal is sensed. Line voltage is selected with the knob, setting the over and under voltage trip points. Voltage range is automatically selected by the microcontroller.

LED Indicator	
Steady Green	Energized
Steady Red	De-engergized (tripped on fault)
Flashing Green	Trip Delay
Alternate Flashing Red/Green	Phase Reversal

Features & Benefits

r cataros a Bononto	
BENEFITS	
Small footprint with universal mounting: ideal replacement for hundreds of competitive part numbers.	
Constant monitoring of single-phase, low voltage, high voltage, voltage unbalance, phase reversal.	
Quick visual indicator for cause of trip. LED indications include: normal operation, trip delay, phase reveral, fault	
Allows control of loads for AC voltages	
Allows flexibility across wide range of systems	
Complies with safety codes for elevators, escalators, moving walkways	
Complies with safety codes for motors and generators	
Complies with safety codes for surge and voltage protection	



PLMU11

Accessories



BZ1 Front Panel Mount Kit

Provides an easy method of through-the-panel mounting of 8-pin or 11-pin plug-in timers, flashers, and other controls.



OT08PC Octal 8-pin Socket

8-pin 35mm DIN rail or surface mount. Rated at 10A @ 600VAC. Surface mounted with two #6 screws or snaps onto a 35 mm DIN rail.



LPSM003ZXID (Indicating), LPSM003Z (Non-indicating) Fuse Holders

Littelfuse POWR-SAFE Dead Front holders provide optimum protection to personnel for Class CC and Midget-Style fuses. 600 VAC/DC



0KLK002.T Midget Fuse (2 Amp)

10 x 38 fast acting, high-interrupting capacity, current-limiting type fuse. 600 Vac/500 Vdc



C103PM (AL) DIN Rail

35 mm aluminum DIN rail available in a 36 in. (91.4 cm) length.

Specifications

Line Voltage

Type 3-phase delta or wye with no connection

to neutral

Line Voltage 200 to 480VAC $\pm 15\%$, 50/60 Hz ± 2 Hz

Adjustable Voltage Ranges

(Automatic Range Selection) 200 to 240VAC, 50/60 Hz

340 to 420VAC, 50 Hz 400 to 480VAC, 60 Hz

Maximum Voltage 552VAC **Phase Sequence** ABC **Power Consumption** $\leq 5W$

Overvoltage, Undervoltage, & Voltage Unbalance

Type Voltage detection with delayed trip and

automatic reset

Overvoltage & Undervoltage

Undervoltage Trip Point

88 - 92% of adjusted line voltage Reset Voltage +2% of trip voltage

Overvoltage Trip Point 109 - 113% of adjusted line voltage

Reset Voltage -2% of trip voltage Voltage Unbalance Trip Point Adjustable from 2 - 10%

Reset on Balance (%)

Selected Unbalance 5 6 1.5 2.5 3.5 4.5 5.4 6.3 7.2 8.1

Reset

Trip Delay Range Adjustable from 0.25 - 30s Severe Unbalance -

2X Selected Unbalance

0.25 - 2s; disabled when the trip delay is

less than 2s ≈ 0.6s

Random Start Delay

Phase Reversal & Phase

Loss Trip Time ≤ 150ms **Phase Loss Setpoint** ≥ 15% unbalance **Reset Type** Automatic

Output Type Energized when voltages are acceptable

Electromechanical relay Type

Form Isolated, SPDT

Rating 10A resistive @ 240VAC; 1/4 hp @ 125VAC;

1/3 hp @ 250VAC; max. 277VAC

Life Mechanical - 1 x 10⁶; Electrical - 1 x 10⁵

Protection

IEEE C62.41-1991 Level B Surge **Isolation Voltage** ≥ 2500V RMS input to output

Mechanical

Mounting* Plug-in socket rated 600VAC

Termination Octal 8-pin plug-in

Dimensions H 77.0 mm (3.03"); **W** 60.7 mm (2.39");

D 45.2 mm (1.78")

Environmental

Operating/Storage

Temperature -40° to 60°C / -40° to 85°C

Weight $\approx 8.6 \text{ oz} (244 \text{ g})$

^{*}CAUTION: Select an octal socket rated for 600VAC operation.