


# **Preliminary Technical Information**

# Trench<sup>™</sup> Power MOSFET Common-Gate Pair

# IXTL2x180N10T

(Electrically Isolated Back Surface)


N-Channel Enhancement Mode Avalanche Rated Fast Intrinsic Rectifier



Symbol	Test Conditions	Maximum Ra	Maximum Ratings		
V <sub>DSS</sub> V <sub>DGR</sub>	$T_J = 25$ °C to 175°C $T_J = 25$ °C to 175°C, $R_{gs} = 1M\Omega$	100 100	V		
V <sub>GSS</sub> V <sub>GSM</sub>	Continuous Transient	± 20 ± 30	V V		
I <sub>D25</sub> I <sub>L(RMS)</sub>	$T_{c} = 25^{\circ}C$ External Lead Current Limit $T_{c} = 25^{\circ}C$ , Pulse Width Limited by $T_{JM}$	100 75 450	A A A		
I <sub>A</sub> E <sub>AS</sub>	$T_{c} = 25^{\circ}C$ $T_{c} = 25^{\circ}C$	25 750	A mJ		
P <sub>D</sub>	T <sub>C</sub> = 25°C	150	W		
dv/dt	$I_{_{\mathrm{S}}} \leq I_{_{\mathrm{DM}}},  V_{_{\mathrm{DD}}} \leq V_{_{\mathrm{DSS}}},  T_{_{\mathrm{J}}} \leq 175^{\circ}\mathrm{C}$	3	V/ns		
T <sub>J</sub> T <sub>JM</sub> T <sub>stg</sub>		-55 +175 175 -55 +175	0° 0° 0°		
T <sub>L</sub> T <sub>SOLD</sub>	1.6mm (0.062 in.) from Case for 10s Plastic Body for 10s	300 260	°C		
F <sub>c</sub>	Mounting Force	20120 /927	N/lb.		
Weight		8	g		

Symbol	•			cteristic Values			
$(T_{J} = 25^{\circ}C)$	Unless Otherwise Specified)		Min.	Тур.	Max	·	
BV <sub>DSS</sub>	$V_{GS} = 0V, I_{D} = 250\mu A$		100			V	
V <sub>GS(th)</sub>	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$		2.5		4.5	V	
I <sub>GSS</sub>	$V_{GS} = \pm 20V, V_{DS} = 0V$				± 200	nA	
I <sub>DSS</sub>	$V_{DS} = V_{DSS}, V_{GS} = 0V$				5	μΑ	
		$T_J = 150^{\circ}C$			250	μΑ	
R <sub>DS(on)</sub>	$V_{GS} = 10V, I_{D} = 50A, Note 1$				9	mΩ	

 $V_{DSS} = 100V$   $I_{D25} = 2x100A$   $R_{DS(op)} \le 9m\Omega$ 



### **Features**

- Silicon Chip on Direct-Copper Bond (DCB) Substrate
- Isolated Mounting Surface
- 2500V~ Electrical Isolation
- 175°C Operating Temperature
- Avalanche Rated
- High Current Handling Capability
- Fast Intrinsic Rectifier
- $\bullet$  Low  $R_{DS(on)}$  and  $Q_{G}$

### **Advantages**

- High Power Density
- Easy to Mount
- Space Savings

### **Applications**

- Automotive
  - Motor Drives
  - DC/DC Conversion
  - 42V Power Bus
  - ABS Systems
- DC/DC Converters and Off-Line UPS
- Primary Switch for 24V and 48V Systems
- High Current Switching Applications
- Distributed Power Architechtures and VRMs
- · Electronic Valve Train Systems
- High Voltage Synchronous Recifier



Symbol	Test Conditions	Chara	Characteristic Values		
$(T_J = 25^{\circ}C, U)$	Inless Otherwise Specified)	Min.	Тур.	Max.	
g <sub>fs</sub>	$V_{DS} = 10V, I_{D} = 60A, \text{ Note 1}$	70	110	S	
C <sub>iss</sub>			6900	pF	
C <sub>oss</sub>	$V_{GS} = 0V, V_{DS} = 25V, f = 1MHz$		923	pF	
C <sub>rss</sub>			162	pF	
$\mathbf{R}_{Gi}$	Gate Input Resistance		3.0	Ω	
t <sub>d(on)</sub>			33	ns	
t <sub>r</sub>	Resistive Switching Times		54	ns	
t <sub>d(off)</sub>	$V_{gs} = 10V, V_{DS} = 0.5 \cdot V_{DSS}, I_{D} = 25A$ $R_{g} = 3.3\Omega$ (External)		42	ns	
t <sub>f</sub>			31	ns	
Q <sub>g(on)</sub>			151	nC	
Q <sub>gs</sub>	$V_{GS} = 10V, V_{DS} = 0.5 \cdot V_{DSS}, I_{D} = 25A$		39	nC	
$Q_{gd}$			45	nC	
R <sub>thJC</sub>				1.0 °C/W	
R <sub>thCS</sub>			0.15	°C/W	

# ISOPLUS I5-Pak<sup>TM</sup> (IXTL) Outline 1,5 = Drain 2,4 = Source 3 = Gate 6 = Isolated

	INCHES		MILLIMETERS			
SYM	MIN	MAX	MIN	MAX		
A	.190	.205	4,83	5.21		
A1	.102	.118	2,59	3.00		
A2	.046	.055	1.17	1,40		
ь	.045	.055	1.14	1,40		
b1	.063	.072	1.60	1.83		
b2	.100	.110	2.54	2.79		
b3	.058	.068	1.47	1.73		
С	.020	.029	0.51	0.74		
D	1.020	1.040	25.91	26.42		
Е	.770	.799	19.56	20.29		
e	.150 BSC		3.81	3.81 BSC		
L	.780	.820	19.81	20.83		
L1	.080	.102	2.03	2.59		
۵	.210	.235	5.33	5.97		
Q1	.490	.513	12.45	13,03		
R	.150	.1BD	3.81	4.57		
R1	.100	.130	2,54	3,30		
S	.668	.690	16_97	17.53		
Т	<b>.</b> 801	.821	20.34	20.85		
U	.065	.D80.	1.85	2.03		

### Source-Drain Diode

SymbolTest ConditionsChara $(T_J = 25^{\circ}C, Unless Otherwise Specified)$ Min.		cteristic Typ.	Values Max.	
I <sub>s</sub>	$V_{GS} = 0V$		180	Α
I <sub>SM</sub>	Repetitive, Pulse Width Limited by $T_{_{\rm JM}}$		450	Α
V <sub>SD</sub>	$I_F = 50A$ , $V_{GS} = 0V$ , Note 1		1.0	V
t <sub>rr</sub>	$I_F = 25A, V_{GS} = 0V$ -di/dt = 100A/ $\mu$ s, $V_R = 50V$	60		ns

Note 1. Pulse test,  $t \le 300\mu s$ , duty cycle,  $d \le 2\%$ .

### PRELIMINARY TECHNICAL INFORMATION

The product presented herein is under development. The Technical Specifications offered are derived from data gathered during objective characterizations of preliminary engineering lots; but also may yet contain some information supplied during a pre-production design evaluation. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

