Special Application Fuses 242 Series Barrier Fuse

242 Series Barrier Fuse





Agency Approvals

Agency	Agency File Number	Ampere Range
c FL °us	E10480	0.040A - 0.250A

Electrical Characteristics

% of Ampere Rating	Opening Time
100%	4 hours, Minimum
300%	10 seconds, Maximum
1000%	0.002 seconds, Maximum

Description

The 242 Series fuse is designed for barrier circuits in intrinsic safety applications relating to Hazardous Locations. Ranging from 40mA to 250mA, the 242 Series provides overcurrent protection solutions to fit many Hazardous Location barrier applications.

Features

- High interrupting rating suitable for intrinsic safety protection of hazardous locations equipment.
- Available in both axial lead and surface mount.
- RoHS compliant and Halogen-free.

Applications

- Intrinsic saftey electrical equipment; Electrical connections and components; Test equipment
- Barriers providing intrinsically safe outputs to Hazardous Locations

Additional Information







es Samples


Electrical Characteristics

Ampere Rating (A)	Body	Interrupting	Nominal Cold	Nominal Melting	Agency Approvals	
	Amp Code	Color Coding	Rating	Resistance (Ohms)	I ² t (A ² Sec.)	c Tus
0.040	.040	Gold		16.48	0.000078	x
0.050	.050	Red	4000A @	11.34	0.000103	х
0.080	.080	Green		8.19	0.000214	x
0.100	.100	Blue		3.60	0.000977	x
0.125	.125	Orange	250VAC/VDC	3.78	0.001026	x
0.160	.160	Violet		3.00	0.00157	x
0.200	.200	Brown		2.68	0.0025	x
0.250	.250	Black		1.6	0.00579	x

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.




Temperature De-Rating Curve 140% 120% 80% 60% 40% 20% -55 -35 -15 5 25 46 65 85 105 125 Temperature (°C)



Soldering Parameters

Reflow Condition		Pb – Free assembly
	-Temperature Min (T _{s(min)})	150°C
Pre Heat	-Temperature Max (T _{s(max)})	200°C
	-Time (min to max) (t _s)	60 – 180 secs
Average ramp up rate (Liquidus Temp (T _L) to peak		5°C/second max
T _{S(max)} to T _L - Ramp-up Rate		5°C/second max
Reflow	-Temperature (T _L) (Liquidus)	217°C
nellow	-Temperature (t _L)	60 – 150 seconds
PeakTemperature (T _P)		250 ^{+0/-5} °C
Time within 5°C of actual peakTemp. (t _p)		20 – 40 seconds
Ramp-down Rate		5°C/second max
Time 25°C to peakTemperature (T _P)		8 minutes Max.
Do not exceed		260°C



Wave Soldering	260°C, 10 seconds max.
----------------	------------------------

Material Information


Body	Ceramic
Leads	Tin-Plated Copper
Endcaps	Silver-Plated Brass


Product Characteristics


Operating Temperature	-40°C to 125°C (Consider rerating)
Thermal Shock	Withstands 5 cycles of – 55°C to 125°C
Vibration	Per MIL-STD-202 Method 201
Insulation Resistance (After Opening)	Greater than 10,000 ohms.

Special Application Fuses 242 Series Barrier Fuse

Dimensions







Part Numbering System



HAT1 = 100 pcs, Axial Leaded, Ammo Pack T1 Tape UAT1 = 500 pcs, Axial Leaded, Ammo Pack T1 Tape UR = 500 pcs, Surface Mount, Tape & Reel