Special Application Fuses

Intrinsically Safe > Surface Mount > 308 Series

308 Series 30V Intrinsically Safe Fuse















Agency Approvals

Agency	Agency File Number	Ampere Rating
€x>	DEMKO 15 ATEX 1439U	0.250A – 1.5A
c FL us	E358130	0.250A – 1.5A
IEC TECEX	IECEx UL 15.0011U (Ex ia IIC)	0.250A – 1.5A

Reference Standards

Certification	Standards		
ATEX	EN 60079-0, EN 60079-11		
IECEx	IEC 60079-0, IEC 60079-11		
UL	UL 913, UL 60079-0, UL 60079-11		
cUL	CAN/CSA C22.2 No. 157, CAN/CSA C22.2 No. 60079-0, CAN/CSA C22.2 No. 60079-11		

Electrical Characteristics for Series

% of Ampere Rating	Opening Time	
100%	4 Hours, Minimum	
250%*	120 Seconds, Maximum	
350%**	60 Seconds, Maximum	

^{*} Applicable to 750mA - 1.5A ** Applicable to 250mA - 1.5A

Description

The 308 Series offers a range of surface mountable encapsulated fuses certified as intrinsically safe components that can be used in hazardous locations. Ideal for use in oil, gas, mine, chemical, pharmaceutical and process industries, the 308 Series surface mountable fuse was designed to limit the energy and temperature generated during its operation. The fuse design and its encapsulant are suitable for use in intrinsically safe apparatus and associated apparatus for peak voltage not exceeding 30V.

Features

- Surface Mountable
- Encapsulated and sealed (0.7mm minimum)
- Designed for operation in a range of hazardous area applications requiring 30V peak
- RoHS-compliant and lead-
- Fully compatible with lead-free solder alloys and higher temperature profiles associated with lead-free assembly
- Suitable for use in Class I, Groups A, B, C and D; Class II, Groups E, F and G; Class III and Class I, Zone O, AEx ia IIC Hazardous Locations.
- Suitable for use in Gas, Zone 0 Hazardous Locations per IEC and EN 60079 Series

Applications

- Testing, measuring or processing electronic and electrical equipment
- Motor controllers
- Communication handsets/ two-way radios
- · Process control and automation
- Sensors
- Lighting
- Flow/gas meters

Electrical Specifications by Items


0.11	Ampere			Nominal Minimum Cold	Minimum Cold	Minimum Cold	Nominal Cold	Agency Approvals		
Catalog Number	Rating (A)	Amp Code	Interrupting Rating	Melting I²t (A² Sec.)	Resistance at -20°C (Ohms)	Resistance at -40°C (Ohms)	Resistance at 25°C (Ohms)	(Ex)	c Al °us	IEC TEČEX
308.25	0.25	0.25	50A@24VAC 50A@30VDC	0.004	1.856	1.821	2.29	Х	Х	X
308.375	0.375	0.375		0.01	1.022	1.006	1.33	Х	X	X
308.5	0.5	0.5		0.022	0.712	0.676	0.908	X	X	X
308.75	0.75	0.75		0.048	0.52	0.511	0.665	Х	Х	Х
308001.0	1.0	1.0		0.1	0.226	0.216	0.42	X	X	X
3081.25	1.25	1.25		0.22	0.24	0.236	0.318	Х	Х	Х
30801.5	1.5	1.5		0.333	0.182	0.144	0.209	Χ	X	X

- 1. The fuse must be mounted so that creepage and clearance distances aren't impaired in any way.
- 2. The fuse is suitable for use in intrinsically safe equipment and associated apparatus for voltage not exceeding 30V peak.
- 3. Maximum surface temperature rise at 170% rated current: 250-375mA = 23°C, 500mA = 35°C, 750mA = 53°C, 1A = 38°C, 1.25-1.50A = 96°C.
- 4. Minimum Cold Resistance at -30°C is available upon request.

Special Application Fuses

Intrinsically Safe > Surface Mount > 308 Series

Temperature Rerating Curve




Notes:

1. Re-rating depicted in this curve is in addition to the standard re-rating of 20% for continuous operation.

Example: For continuous operation at 55°C, the fuse should be rerated as follows: $\frac{1}{100}$ $\frac{1}{100}$ $\frac{1}{100}$ $\frac{1}{100}$ $\frac{1}{100}$ $\frac{1}{100}$


2. The temperature rerating curve represents the nominal conditions. For questions about temperature rerating curve, please consult Littelfuse technical support for assistance.

Average Time Current Curves




Soldering Parameters

Reflow Con	Pb – Free assembly		
	-Temperature Min (T _{s(min)})	150°C	
Pre Heat	-Temperature Max (T _{s(max)})	200°C	
	-Time (Min to Max) (t _s)	60 – 180 secs	
Average ran	3°C/second max.		
T _{S(max)} to T _L	3°C/second max.		
Reflow	-Temperature (T _L) (Liquidus)	217°C	
	-Temperature (t _L)	60 – 150 seconds	
Peak Tempe	260+0/-5 °C		
Time within	30 Sec Max		
Ramp-dowr	6°C/second max.		
Time 25°C t	8 minutes max.		
Do not exce	-		



Special Application Fuses


Dimensions (mm)



Part Marking System

Marking Code	Amp Code		
D	0.250		
E	0.375		
F	0.500		
G	0.750		
Н	001.0		
J	1.25		
К	01.5		

Part Numbering System



Packaging			
Packaging Option	Packaging Specification	Quantity	Quantity and Packaging Code
12mm Tape and Reel	EIA 481-1	500	UR

Product Characteristics

	Polyamide 6T/66		
Molding Material	CTI 100 volts minimum		
	Continuous Operating Temperature: 140°C		
Ambient Temperature 12	-40°C to +70°C		
Terminations	Tin-Plated Silver-Plated Copper		
Thermal Shock	Withstands 100 cycles of -55°C to 125°C		
Vibration	MIL-STD-202, Method 201		
Mechanical Shock	MIL-STD-202, Method 213, Condition A		
Moisture Resistance	MIL-STD-202, Method 106		
Salt Spray	MIL-STD-202, Method 101, Condition B		
Resistance to Soldering Heat	MIL-STD-202, Method 210, Condition K		

Notes

- Any use of the 308 Series fuse outside of the ambient temperature range specified in the table is subject to additional investigation.
- additional investigation.

 2. Specified ambient temperature range is for intrinsic safety certification.