



SP3312T Series 3.3V 15A Diode Array



Pinout



Functional Block Diagram



Description

The SP3312T integrates 4 channels (2 differential pair) of low capacitance diodes to protect sensitive I/O pins against lightning induced surge events and ESD. This robust component can safely absorb up to 15A per IEC 61000-4-5 ($t_p=8/20\mu s$) without performance degradation and a minimum $\pm 30kV$ ESD per IEC 61000-4-2 international standard. The low loading capacitance makes the SP3312T ideal for protecting high-speed signal pins.

Features

- ESD, IEC 61000-4-2, $\pm 30kV$ contact, $\pm 30kV$ air
- EFT, IEC 61000-4-4, 40A ($t_p=5/50ns$)
- Lightning, IEC 61000-4-5 2nd edition, 15A ($t_p=8/20\mu s$)
- Low capacitance of 1.3pF (TYP) per I/O
- Low leakage current of $0.01\mu A$ (TYP) at 3.3V
- Low variation in capacitance vs. bias voltage: 0.3pF Typical ($V_R=0$ to 2.5V)
- AEC-Q101 qualified
- Moisture Sensitivity Level (MSL-1)

Applications

- 10/100/1000 Ethernet
- Integrated magnetics/RJ45 connectors
- LAN/WAN Equipment
- Security Cameras
- Industrial Controls
- Notebook & Desktop Computers

Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

Absolute Maximum Ratings

Symbol	Parameter	Value	Units
I_{PP}	Peak Current ($t_p=8/20\mu s$)	15.0	A
P_{PK}	Peak Pulse Power ($t_p=8/20\mu s$)	250	W
T_{OP}	Operating Temperature	-40 to 125	°C
T_{STOR}	Storage Temperature	-55 to 150	°C

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

Thermal Information

Parameter	Rating	Units
Storage Temperature Range	-55 to 150	°C
Maximum Junction Temperature	150	°C
Maximum Lead Temperature (Soldering 20-40s)	260	°C


Electrical Characteristics ($T_{OP}=25^\circ C$)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}				3.3	V
Snap Back Voltage	V_{SB}	$I_{SB}=50mA$	2.8			V
Reverse Leakage Current	I_{LEAK}	$V_R=3.3V$, I/O to GND		0.01	0.05	μA
Clamp Voltage ¹	V_C	$I_{PP}=1A$, $t_p=8/20\mu s$, Fwd		6.0		V
		$I_{PP}=2A$, $t_p=8/20\mu s$, Fwd		7.0		V
		$I_{PP}=10A$, $t_p=8/20\mu s$, Fwd		13.0		V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p=100ns$, I/O to GND		0.40		Ω
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact)	± 30			kV
		IEC 61000-4-2 (Air)	± 30			kV
Variation in Capacitance with Reverse Bias ¹		Pins 1, 8 to 2, 7 and pins 3, 6 to 4, 5 $V_R=0$ to 2.5V, $f=1MHz$		0.3	2.0	pF
Diode Capacitance ¹	$C_{I/O-GND}$	Reverse Bias=0V		1.3	4.0	pF


Note:

- Parameter is guaranteed by design and/or component characterization.
- Transmission Line Pulse (TLP) with 100ns width, 2ns rise time, and average window $t1=70ns$ to $t2=90ns$


Clamping Voltage vs I_{PP}




Capacitance vs. Reverse Bias



Transmission Line Pulsing (TLP) Plot




8/20µs Pulse Waveform



Soldering Parameters

Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 180 secs
Average ramp up rate (Liquidus) Temp (T_L) to peak		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Temperature (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/5} °C
Time within 5°C of actual peak Temperature (t_p)		20 – 40 seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes Max.
Do not exceed		260°C



Product Characteristics

Lead Plating	Pre-Plated Frame
Lead Material	Copper Alloy
Lead Coplanarity	0.004 inches(0.102mm)
Substrate material	Silicon
Body Material	Molded Compound
Flammability	UL Recognized compound meeting flammability rating V-0


Notes :

1. All dimensions are in millimeters
2. Dimensions include solder plating.
3. Dimensions are exclusive of mold flash & metal burr.


Ordering Information

Part Number	Package	Marking	Min. Order Qty.
SP3312TUTG	µDFN-08	33H	3000





Part Numbering System



Part Marking System




Package Dimensions — μDFN-08



Package	μDFN-08 (2.0x1.0mm)			
JEDEC	MO-229			
Symbol	Millimeters		Inches	
	Min	Max	Min	Max
A	0.45	0.55	0.018	0.022
A1	0	0.05	0	0.002
b	0.20	0.30	0.008	0.012
D	1.90	2.10	0.075	0.083
E	0.90	1.10	0.035	0.043
R	0.10 BSC		0.004 BSC	
e	0.50 BSC		0.020 BSC	
L	0.30	0.40	0.012	0.016

Embossed Carrier Tape & Reel Specification — μDFN-08



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.