



RESISTANCE @ +25°C = 100,000 Ω ± 5%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 10 SECONDS NOMINAL
 TEMPERATURE RATING = -80 TO +150°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

---	ISO RELEASE	04/16/03	DD
"A"	CHANGED DIAMETER	02/07/95	RD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT U.S. SENSOR CORP. 714-639-1000 www.ussensor.com
DRAWN BY	T. SOMERVILLE	
DATE	06/03/93	NTC THERMISTOR
REV.	"A"	
LAYER	0 OF 2	P/N SC104J4J