

PolySwitch® PTC Devices

Overcurrent Protection Device

PRODUCT: MXP370BD

DOCUMENT: SCD27591 REV LETTER: C

REV DATE: JULY 26, 2016 PAGE NO.: 1 OF 2

Specification Status: Released


Maximum Electrical Rating
Operating Voltage: 6Vdc MAX
Interrupt Current: 50A MAX


Chip Size: 3 X 4 mm nominal

Leads: Nickel 1/2H

0.1mm nominal thickness

Solder: Lead-free





[]] Coating Area

TABLE I. DIMENSIONS:

	Α		В		С)	E		F	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	10.5	11.3	2.96	3.26	0.7	1.1	2.0	-	2.0	-	2.2	2.4
in*:	(0.41)	(0.44)	(0.11)	(0.12)	(0.02)	(0.04)	(0.07)		(0.07)		(80.0)	(0.09)

^{*}Rounded off approximation

TABLE II. PERFORMANCE RATINGS: As measured in Mueller Kelvin Clips model BU-75K.

I		CURRENT TRIP LIMITS										REFE	RENC	ONE-H	HOUR	TRIPPED
HOLE)											E POST-TRIF			-TRIP	-STATE
												RESISTANC RESISTANC			POWER	
												E		E		DISSIPA
																TION
AMP	^ ^ ^	AMPS AT-20 °C		AMPS AMPS AMPS		AMPS AMPS		5	SECONDS	OHMS		OHMS		WATTS		
S				_		_		AT 60°C		-	AT 25°C,	AT 25°C		AT 25°C		AT
25°C	; '^ -					A1 00 C		AT 70°C		18.5A	A1 25 C		A1 25 C		25°C, 6V	
ноі г	HOLD	TDID	HOLD	TDID	HOL	TRIP	HOLD	TDID	HOLD	TRI	MAX	MIN	MAX	MIN	MAX	MAX
IIOLL	JIIOLD	HXII	IOLD	11311	D		IIOLD	11711	IIOLD	Р	IVIAX	IVIIIN	IVIAA	IVIIIN	IVIAA	IVIAA
3.7	6.0	15.3	5.0	12.1	3.7	9.0	1.9	4.8	1.6	3.7	5	0.004	0.010	0.004	0.016	1.3

Agency Recognitions: UL, TUV, CSA

Reference Documents: PS300

Precedence: This specification takes precedence over documents referenced herein.

Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

MATERIALS INFORMATION:

ROHS Compliant

ELV Compliant

Pb-Free

Directive 2002/95/EC Compliant Directive 2000/53/EC Compliant





PolySwitch® PTC Devices

Overcurrent Protection Device

PRODUCT: MXP370BD

DOCUMENT: SCD27591 REV LETTER: C

REV DATE: JULY 26, 2016

PAGE NO.: 2 OF 2

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.