Phase Control



Description

The PHS series relays are designed for changing lamp intensity, varying the speed of a fan, or controlling the temperature of a heater. The effective output voltage is adjusted with an accessory external potentiometer suitable for line voltage applications.

Operation

Upon application of input voltage, effective output voltage can be adjusted by changing the external resistance value. As the external resistance increases, the effective output voltage decreases, and the inverse is also true.

Features & Benefits

FEATURES	BENEFITS	
External adjustment – potentiometer rated at 230 V ac	Allows direct control of heavy loads	
Up to 20 A steady state – 200 A inrush	Allows direct control of heavy loads	
Single hole surface mounting	Provides quick and easy installation	
Solid-state design	Longer life	

Applications

• Protection, control and/or monitoring of generators and other devices



۶Ľ

Specifications

- Output			
Туре	Variable voltage phase angle control		
Rating	Steady State (at 100 % On)	Inrush*	
-	1 A	10 A	
	6 A	60 A	
	10 A	100 A	
	20 A	200 A	
Minimum Load	Current 100 mA		
Voltage Drop	≅ 2.0 V at rated current		
Input			
Voltage	120 or 230 V ac		
Tolerance	±20%		
AC Line	Frequency 50/60 Hz		
Protection			
Output Contact Rating-SPST	A300, 720VA @ 240 V ac (10 A max.)		
General Characteristics			
Dielectric Breakdown	\ge 2000 V RMS terminals to mounting surface		
Insulation Resistance	≥100MΩ		
Mechanical			
Mounting *	Surface mount with one #10 (M5 x 0.8) screw		
Dimensions	H 50.8 mm (2"); W 50.8 mm (2"); D 38.4 mm (1.51")		
Termination	0.25 in. (6.35 mm) male quick connect terminals		
Environmental			
Operating/Storage Temperature	-20 °C to 60 °C / -40 °C to 85 °C		
Humidity	95% relative, non-condensing		
Weight	1 A: ≅ 2.4 oz (68 g)		
	6, 10, & 20 A: ≅ 3.9 oz (111 g)		
External Adjustment Potentiometer			
120 V ac	100KΩ rated at 1W		
230 V ac	$200 \text{K}\Omega$ rated at 2W; Must have insulation resistance suitable for line voltage applications.		

*Units rated > 6 A must be bolted to a metal surface using the included heat sink compound. The maximum mounting surface temperature is 90 °C. Inrush: Non-repetitive for 16 ms.

Certification & Compliance

UL Recognized

File E57310 UL508

Accessories

P1004-174 (100kΩ 1W), **P1004-175** (200kΩ 2W) **Versa-Pot** Panel mountable, industrial potentiometer recommended for remote time delay adjustment.

P0700-7 Versa-Knob

Designed for 0.25 in (6.35 mm) shaft of Versa-Pot. Semi-gloss industrial black finish.

P1015-64 (AWG 14/16) Female Quick Connect

These 0.25 in. (6.35 mm) female terminals are constructed with an insulator barrel to provide strain relief.

P1015-18 Quick Connect to Screw Adapter

Screw adapter terminal designed for use with all modules with 0.25 in. (6.35 mm) male quick connect terminals.




Ordering Information

MODEL	INPUT VOLTAGE	RATING
PHS120A10	120 V ac	10 A
PHS120A20	120 V ac	20 A
PHS120A6	120 V ac	6 A
PHS230A10	230 V ac	10 A
PHS230A20	230 V ac	20 A
PHS230A6	230 V ac	6 A


If you don't find the part you need, call us for a custom product 800-843-8848

Dimensions Inches (mm)






Wiring Diagram



Typical Output Waveform



Disclaimer Notice – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littlefuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littlefuse.com/product-disclaimer.

