# **Protection Relays Current Monitoring Relays and Transducers**



# TCS SERIES


## **Current Sensor**






# Wiring Diagram


## POSITIVE SWITCHING








#### **SINKING**



## SOURCING



# **Description**

The TCS Series is a low cost method of go/no go current detection. It includes a solid-state output to sink or source current when connected directly to a standard PLC digital input module. Its normally open or normally closed output can also be used to control relays, lamps, valves, and small heaters rated up to 1A steady, 10A inrush. The TCS is self-powered (no external power required to operate the unit) and available with an adjustable actuation range of 2 - 20A or factory fixed actuation points from 2 - 45A.

#### Operation

Normally Open: When a current equal to or greater than the actuate current is passed through the toroidal sensor, the output closes. When the current is reduced to 95% of the actuate current or less, the output opens.

Normally Closed: When the current through the toroid is equal to or greater than the actuate current, the output opens. When the current is reduced below 95% of the actuate current, the output closes. To increase sensitivity, multiple turns may be made through the TCS's toroidal sensor. The trip point range is divided by the number of turns through the toroidal sensor to create a new range. When using an external CT, select a 2VA, 0-20A output CT rated for the current to be monitored. Select TCS adjustment range 0. Pass one secondary wire lead through the TCS' toroid and connect the secondary leads together.

## **Features & Benefits**

FEATURES	BENEFITS			
Self powered	No control voltage is required to operate the unit			
Totally solid state and encapsulated	No moving parts to arc and wear out over time and encapsulated to protect against shock, vibration, and humidity			
Can connect directly to PLC	Solid state output to sink or source current can be connected directly to a standard PLC digital input module			
1A steady, 10A inrush solid-state output	Provides 100 million operations in typical conditions			
Complete isolation between sensed current and control circuit	Allows you to monitor a load in a separate lectrical system			

# **Ordering Information**

MODEL	OUTPUT VOLTAGE	ACTUATE CURRENT	OUTPUT FORM	MODEL	OUTPUT VOLTAGE	ACTUATE CURRENT	OUTPUT FORM
TCSG2A	3 to 50VDC	Fixed, 2A	Normally open	TCSH2B	24 to 240VAC	Fixed, 2A	Normally closed
TCSGAA	3 to 50VDC	2-20A adjustable	Normally open	TCSH5B	24 to 240VAC	Fixed, 5A	Normally closed
TCSGAB	3 to 50VDC	2-20A adjustable	Normally closed	TCSHAA	24 to 240VAC	2-20A adjustable	Normally open
TCSH2A	24 to 240VAC	Fixed, 2A	Normally open	TCSHAB	24 to 240VAC	2-20A adjustable	Normally closed

If you don't find the part you need, call us for a custom product 800-843-8848

# Littelfuse® Expertise Applied | Answers Delivered

# TCS SERIES

## **Accessories**



#### P1023-6 Mounting bracket

The 90° orientation of mounting slots makes installation/removal of modules quick and easy.



# **P1015-64** (AWG 14/16)

#### Female Quick Connect

These 0.25 in. (6.35 mm) female terminals are constructed with an insulator barrel to provide strain relief.



#### P1015-18 Quick Connect to Screw Adapter

Screw adapter terminal designed for use with all modules with 0.25 in. (6.35 mm) male quick connect terminals.



#### C103PM (AL) DIN Rail


35 mm aluminum DIN rail available in a 36 in. (91.4 cm) length.



## P1023-20 DIN Rail Adapter

Allows module to be mounted on a 35 mm DIN type rail with two #10 screws.

# **Function Diagram**



TP = Trip Point

OC = Monitored Current

NO = Normally Open Output

NC = Normally Closed Output

R = Reset

# **Specifications**

#### Sensor

Type

Current to Actuate

Toroid, through hole wiring, alternating current, monitored wire must be properly insulated Adjustable: - 2 - 20A, guaranteed range

Fixed: - 2 - 45A, +0/-20%

Reset Current  $\approx 95\%$  of the actuate current

Maximum Allowable Current Steady - 50A turns Inrush - 300A turns for 10s

Actuate Current vs. Temp.

& Voltage  $\leq \pm 5\%$ 

**Response Times** Overcurrent -  $\leq$  200ms Undercurrent -  $\leq$  1s

Burden < 0.5VA

Output

Type Solid state Form NO or NC

 Rating
 1A steady, 10A inrush

 Voltage
 AC - 24 to 240VAC +10/-20%

DC - 3 to 50VDC **IE Drop** AC NO & NC -  $\cong$  2.5V

**Voltage Drop** AC NO & NC -  $\cong$  2.5V DC NO & NC -  $\cong$  1.2V

Protection

**Circuitry** Encapsulated

**Dielectric Breakdown** ≥ 2000V RMS terminals to mounting surface

Insulation Resistance  $\geq 100 \text{ M}\Omega$ 

Mechanical

**Mounting** Surface mount with one #10 (M5 x 0.8) screw

**Dimensions H** 50.8 mm (2"); **W** 50.8 mm (2");

**D** 44.5 mm (1.75")

**Termination** 0.25 in. (6.35 mm) male guick connect

terminals (2)

**Sensor Hole** 0.36 in. (9.14 mm) for up to #4 AWG

(21.1 mm2) THHN wire

**Environmental** 

Operating/Storage

Temperature -20° to 60°C / -40° to 85°C Humidity 95% relative, non-condensing

Weight  $\approx 2.6 \text{ oz } (74 \text{ g})$