
TSD2 SERIES

Interval Timer



Wiring Diagram



R_⊤ is used when external adjustment is ordered.

Ordering Information

	MODEL	INPUT VOLTAGE	ADJUSTMENT	TIME DELAY
	TSD2411S	120VAC	Fixed	1s
	TSD24145S	120VAC	Fixed	45s
	TSD241600S	120VAC	Fixed	600s
	TSD2434	120VAC	Onboard	1 - 100m

If you don't find the part you need, call us for a custom product 800-843-8848

Description

The TSD2 Series is designed for more demanding commercial and industrial applications where small size and accurate performance are required. The factory calibration for fixed time delays is within 1% of the target time delay. The repeat accuracy, under stable conditions, is 0.1% of the time delay. The TSD Series is rated to operate over an extended temperature range. Time delays of 0.1 seconds to 100 hours are available. The output is rated 1A steady and 10A inrush. The modules are totally solid state and encapsulated to protect the electronic circuitry.

Operation (Interval)

Upon application of input voltage, the time delay begins. The output is energized during the time delay. At the end of the time delay, the output de-energizes and remains de-energized until input voltage is removed.

Reset: Removing input voltage resets the time delay and output.

Features & Benefits

FEATURES	BENEFITS	
Microcontroller based	Repeat Accuracy + / - 0.1%, + / -1% time delay accuracy	
Extended temperature range	Rated to 75°C operating temperature to withstand high heat applications.	
Compact, low cost design	Allows flexibility for OEM applications	
1A Steady solid-state output, 10A inrush	Provides 100 million operations in typical conditions.	
Totally solid state and encapsulated	No moving parts to arc and wear out over time and encapsulated to protect against shock, vibration, and humidity	

Accessories



P1004-95, P1004-95-X Versa-Pot

Panel mountable, industrial potentiometer recommended for remote time delay adjustment.



P1023-6 Mounting bracket

The 90° orientation of mounting slots makes installation/removal of modules guick and easy.



P0700-7 Versa-Knob

Designed for 0.25 in (6.35 mm) shaft of Versa-Pot. Semi-gloss industrial black finish.



P1015-64 (AWG 14/16)

Female Quick Connect

These 0.25 in. (6.35 mm) female terminals are constructed with an insulator barrel to provide strain relief.



P1015-18 Quick Connect to Screw Adapter

Screw adapter terminal designed for use with all modules with 0.25 in. (6.35 mm) male quick connect terminals.



TSD2 SERIES

Accessories



C103PM (AL) DIN Rail

35 mm aluminum DIN rail available in a 36 in. (91.4 cm) length.




P1023-20 DIN Rail Adapter

Allows module to be mounted on a 35 mm DIN type rail with two #10 screws.

External Resistance vs. Time Delay





This chart applies to externally adjustable part numbers.

The time delay is adjustable over the time delay range selected by varying the resistance across the RT terminals; as the resistance increases the time delay increases

When selecting an external RT, add the tolerances of the timer and the RT

for the full time range adjustment. **Examples:** 1 to 50 S adjustable time delay, select time delay range 1 and a 50 K ohm RT. For 1 to 100 S use a 100 K ohm RT.

Specifications

Time Delay

Range 0.1s - 100h in 7 adjustable ranges or fixed Repeat Accuracy ±0.1% or 20ms, whichever is greater

≤ ±1%

Tolerance

(Factory Calibration) ≤ ±1% **Reset Time** ≤ 150ms

Time Delay vs. Temperature

& Voltage

Input

Voltage 24, 120, or 230VAC

Tolerance ±20% **AC Line Frequency** 50/60 Hz $\leq 2VA$ **Power Consumption**

Output

Type Solid state

NO, closed during timing Form

Maximum Load Current 1A steady state, 10A inrush at 60°C **Off State Leakage Current** ≅ 5mA @ 230VAC

Voltage Drop Protection

Circuitry Encapsulated

Dielectric Breakdown ≥ 2000V RMS terminals to mounting surface

≅ 2.5V @ 1A

Insulation Resistance $\geq 100 \text{ M}\Omega$ Mechanical

Mounting Surface mount with one #10 (M5 x 0.8) screw

Dimensions H 50.8 mm (2"); **W** 50.8 mm (2");

D 30.7 mm (1.21")

Termination 0.25 in. (6.35 mm) male quick connect

terminals


Environmental

Operating/Storage

Temperature -40° to 75°C / -40° to 85°C Humidity 95% relative, non-condensing

Weight $\approx 2.4 \text{ oz } (68 \text{ g})$

Function Diagaram



V = Voltage NO = Normally **Open Contact**

NC = Normally **Closed Contact**

TD =Time Delay

R = Reset

= Undefined Time