



Expertise Applied | Answers Delivered

# Smart Metering


---




Building Solutions

*Users must independently evaluate the suitability of and test each product selected for their own specific applications. It is the User's sole responsibility to determine fitness for a particular system or use based on their own performance criteria, conditions, specific application, compatibility with other parts, and environmental conditions. Users must independently provide appropriate design and operating safeguards to minimize any risks associated with their applications and products. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [littelfuse.com/disclaimer-electronics](http://littelfuse.com/disclaimer-electronics).*

# Buildings are evolving into networks of electric and electronic systems to help reach net-zero goals



# Smart meters—key to advanced energy management



**Littelfuse: Key know-how to help customers implement more reliable and safer smart meters**

- Electric transients and overcurrent protection
- Anti-tamper solutions
- Flow measurement devices
- Low power consumption sensors
- Load switching and energy pulse out
- Over-temp detection and temperature measurement
- Power management
- Button inputs and controls

Littelfuse can help with cross-functional system-level expertise and application testing

# Market trends of smart meters

## Market trends and drivers

A total of 160 million smart meters were installed globally in 2021; 125 million electricity meters and 35 million gas or water meters


65% of all smart meters are installed in the Asia region, 20% in Europe, and 15% in the Americas

Major benefits of smart meters include detecting leakages, eliminating costly manual readings by municipality personnel, and detecting theft

The transition from gas and oil to electricity for heating, cooking, and transportation is accelerating the deployment of electricity meters

In the United States, Canada, and some countries of Europe, the first-generation smart meters are starting to reach their end of life. Replacement installations expected over the next several years.

## Smart meters installed worldwide annually



Sources: 1. [Smart Meters Market](#)  
2. [Global Smart Electricity Meters Market](#)  
3. Internal marketing estimates

# Smart electricity meter

1

**Anti-tamper**  
Reed Switch, TMR,  
Detect Switch



2

**Metrology System Unit**  
MOV, Fuse, TVS Diode, eFuse,  
SiC MOSFET, PPTC, NTC



**Acronyms:**

TMR: tunneling magnetoresistive

MOV: metal oxide varistor

TVS: transient-voltage suppression

SiC: silicon carbide

PPTC: polymeric positive temperature coefficient

NTC: negative temperature coefficient

SSR: solid state relay



3

**Communication Interface**  
TVS Diode Array,  
SIDACtor®, Opto-isolator






4

**I/O Protection and Control**  
SSR, Fuse, TVS Diode,  
MOV, Tactile Switch



# Electricity meter system block diagram



**Legend:**  
 Power  
 Data

**Acronyms:**  
 AC: alternate current  
 MCU: microcontroller unit  
 GSM: global system for mobile communication  
 PLC: power line communication

	Technology	Product series
1	MOV	<a href="#">Ultra MOV</a> , <a href="#">CIII</a> , <a href="#">TMOV</a>
	Fuse	<a href="#">215</a> , <a href="#">514</a> , <a href="#">835</a>
	TVS Diode	<a href="#">SMAJ</a> , <a href="#">SMBJ</a>
	NTC	<a href="#">End-banded Chip</a>
	MOSFET / SiC MOSFET	<a href="#">Polar™</a> , <a href="#">X2-class</a> /
	PPTC	<a href="#">TRF600-150</a>
	Protection IC (eFuse)	<a href="#">LS0502SCD33</a> , <a href="#">LS2406ERQ23</a>
2	MOSFET	<a href="#">X2-class</a>
	TVS Diode Array	<a href="#">SC1205</a> , <a href="#">SC1210</a>
	SIDACtor®	<a href="#">SEP0xx</a>
	Solid State Relay	<a href="#">PLA192</a> , <a href="#">CPC1394</a> , <a href="#">PLA193</a> , <a href="#">PLA194</a> , <a href="#">CPC1303</a>
3	Tactile Switch	<a href="#">KSC</a> , <a href="#">KSE</a> , <a href="#">PTS</a>
4	Reed Switch / TMR	<a href="#">59177</a> , <a href="#">MDSR-10</a> / <a href="#">TMR</a>
	Detect Switch	<a href="#">SDS</a> , <a href="#">DDS</a>
5	Solid State Relay	<a href="#">PLA192</a> , <a href="#">CPC1394</a> , <a href="#">CPC1983YE</a> , <a href="#">PLA193</a> , <a href="#">PLA194</a>
	TVS Diode / MOV	<a href="#">SMCJ</a> / <a href="#">SM7</a>



Click the product series in the table below for more info

# Benefits of Littelfuse products for electric meters

	Technology	Function in application	Product series	Benefits	Features
1	MOV	Protects power unit from voltage transients and lightning	<a href="#">Ultra MOV</a> , <a href="#">CIII</a> , <a href="#">TMOV</a>	Reduces customer qualification time by complying with third-party safety standards such as UL / IEC	High energy absorption capability: 40–530 J (2 ms)
	Fuse	Protects power stage from overcurrent events	<a href="#">215</a> , <a href="#">514</a> , <a href="#">835</a>	Reduces customer qualification time by complying with third-party safety standards such as UL / IEC	Third-party compliance (UL / IEC); low internal resistance; shock safe; vibration resistant
	TVS Diode	Protects sensitive electronic component from voltage transients	<a href="#">SMAJ</a> , <a href="#">SMBJ</a>	Improves system reliability	1500 W peak pulse capability; compatible with lead-free solder reflow temperature profile
	NTC	Senses temperature of power semiconductor devices	<a href="#">End-banded Chip</a>	SMD form-factor allows for compact design; non-standard resistance values available	Surface mountable; fast thermal response
	MOSFET / SIC MOSFET	Provides high-frequency load switching	<a href="#">Polar™</a> , <a href="#">X2-class</a> /	High power density and low power consumption promotes an efficient design	Dynamic dv/dt rating; low R <sub>DS(ON)</sub> and Q <sub>g</sub> avalanche rate; low package inductance
	PPTC	Protects power stage from overcurrent events	<a href="#">TRF600-150</a>	Low maintenance; compact form-factor saves space	Resettable overcurrent protection; fast time-to-trip resistance; sorted and matched devices available
	Protection IC (eFuse)	Provides OCP, OVP, OTP, and reverse current blocking	<a href="#">LS0502SCD33</a> , <a href="#">LS2406ERQ23</a>	High integration with multiple protections in small package	3–24 V operation voltage and 6 A continuous current with 24 mΩ Ron
	MOSFET	Provides switching function in pre-regulation circuit for charging capacitor	<a href="#">X2-class</a>	Robust switching operation, high power density; extremely low thermal dissipation	Ultra-low on-resistance R <sub>DS(ON)</sub> and gate charge Q <sub>g</sub> ; dv/dt ruggedness; low package inductance
2	TVS Diode Array	Protects wired communication interface from user-induced ESD events	<a href="#">SC1205</a> , <a href="#">SC1210</a>	Promotes robust communication channel operation while maintaining high signal integrity	ESD: IEC 61000-4-2, ±30 kV contact, ±30 kV air, EFT: IEC 61000-4-4, 40 A (5/50 ns)
	SIDACtor®	Protects sensitive electronic components from damage due to lightning surges	<a href="#">SEP0xx</a>	Promotes robust operation of communication channel with minimal impact on signal integrity	Low insertion loss, log-linear capacitance; low clamping voltage
	Solid State Relay	Provides isolation of pulse-out signal between MCU and M-Bus or PLC interface	<a href="#">PLA192</a> , <a href="#">CPC1394</a> ,	High reliability & electrical isolation; robust design; no EMI/RFI generation	Up to 3750 V <sub>RMS</sub> input/output isolation; UL/IEC certified; low drive power
			<a href="#">PLA193</a> , <a href="#">PLA194</a> , <a href="#">CPC1303</a>		
3	Tactile Switch	Switch for triggering display, resetting, etc.	<a href="#">KSC</a> , <a href="#">KSE</a> , <a href="#">PTS</a>	Available in wide range of operating forces; rugged sealing and resistant to corrosion	Ultra-low current consumption; operating life up to 1M cycles
4	Reed Switch	Prevents magnetically induced tampering	<a href="#">59177</a> , <a href="#">MDSR-10</a> / <a href="#">TMR</a>	Lowest power consumption for longest battery life	Hermetically sealed; magnetically operated contacts
	Detect Switch	Detects tampering of the meter casing	<a href="#">SDS</a> , <a href="#">DDS</a>	Compact and reliable tamper detection	Low profile package; available in vertical and horizontal configurations; SMT or through-hole
5	Solid State Relay	Provides isolation from MCU and load output	<a href="#">PLA192</a> , <a href="#">CPC1394</a> , <a href="#">CPC1983YE</a> , <a href="#">PLA193</a> , <a href="#">PLA194</a>	High reliability and electrical isolation; robust design; no EMI/RFI generation	Up to 3750 V <sub>RMS</sub> input/output isolation; UL/IEC certified; low drive power
	TVS Diode / MOV	Protects auxiliary I/O from voltage transients due to overload	<a href="#">SMCJ</a> / <a href="#">SM7</a>	Promotes robust operation maintaining high signal integrity; saves board space	Excellent clamping capability; low incremental surge resistance




# Smart water and gas meter

1

## Battery and Interface Panel

PPTC, Fuse, eFuse, ATEX Fuse, TVS Diode, Tactile Switch



2

## Communication Interface


TVS Diode Array, SIDActor®, SSR



3

## Flow Measurement

NTC Thermistor, Reed Switch



1

ELECTRONICALLY COMPENSATED METER

4

2

3

5

Gas

1 PULSE / 1 M3

INTRINSICALLY SAFE - 500 PPTC INTRINSICALLY SAFE FUSE IN CLASS I GROUP 0 HAZARDOUS LOCATIONS  
TEMP. COEFF. TO AMBIENT TEMP. SEE ONLY FIGURE 10-1  
LITHIUM BATTERY PACK PIN 3A/5500mAh GET MANUAL FOR EXTENDED BATTERY LIFE  
AMBIENT TEMP. RANGE: -40 TO 65°C (-40 TO 149°F)  
TEMP. COMPENSATION RANGE: 25 TO 40°C (77 TO 104°F)  
WARNING: SUBSTITUTION OF COMPONENTS MAY AFFECT PERFORMANCE

4

## Anti-tamper


Reed Switch, TMR, Detect Switch



5


## Safety Valve

Solid State Relay





# Gas and water meters share many functional blocks



	Technology	Product series
1	Fuse	<a href="#">Atex 259 / 304, 437</a>
	PPTC	<a href="#">1812L</a>
	Protection IC (eFuse)	<a href="#">LS0502SCD33, LS2406ERQ23</a>
2	TVS Diode	<a href="#">SMBJ, SMCJ</a>
	TVS Diode Array	<a href="#">SC1205, SC1210</a>
	SIDACtor®	<a href="#">Pxxx0SLR</a>
3	Solid State Relay	<a href="#">PLA192, CPC1394, PLA193, PLA194</a>
	NTC	<a href="#">MELF style, End-banded Chip, Thermistor assembly</a>
4	Reed Switch	<a href="#">MDSR-10</a>
	Reed Switch, TMR	<a href="#">59166, MDMS-4, TMR</a>
5	Detect Switch	<a href="#">SDS, DDS</a>
	Solid State Relay	<a href="#">PLA192, CPC1394, CPC1983YE, PLA193, PLA194</a>
6	Tactile Switch	<a href="#">KSC, KSE, PTS</a>

# Benefits of Littelfuse products for water/gas meters

	Technology	Function in application	Product series	Benefits	Features
1	Fuse	Protects power stage from overcurrent events	<a href="#">259,304, 437</a>	Reduces customer qualification time by complying with third-party safety standards such as UL / IEC	Third-party compliance (UL / IEC); low internal resistance
	PPTC	Protect battery from over current and over temperature events	<a href="#">1812L</a>	Auto resets after fault is removed; allows for compact design	Resettable; low resistance; compact design
	Protection IC (eFuse)	Provides OCP, OVP, OTP, and reverse current blocking	<a href="#">LS0502SCD33, LS2406ERQ23</a>	High integration with multiple protections in small package	3-24 V Operation voltage and 6 A continuous current with 24 mΩ Ron
	TVS Diode	Protects sensitive electronic components from voltage transients	<a href="#">SMBJ, SMCJ</a>	Improves system reliability by protecting downstream components by clamping voltage at safe levels during transients on power lines	1500 W peak pulse capability; compatible with lead-free solder reflow temperature profile
2	TVS Diode Array	Protects wired communication interface from user-induced ESD events	<a href="#">SC1205, SC1210</a>	Promotes robust communication channel operation while maintaining high signal integrity	ESD: IEC 61000-4-2, ±30 kV contact, ±30 kV air, EFT: IEC 61000-4-4, 40 A (5 / 50 ns)
	SIDACtor®	Protects sensitive electronic components from damage due to lightning surges	<a href="#">Pxx0SLR</a>	Promotes robust operation of communication channel with minimal impact on signal integrity	Low insertion loss, log-linear capacitance; combined longitudinal and metallic protection fast clamping; low clamping voltage
	Solid State Relay	Provides isolation of pulse-out signal between MCU and M-Bus	<a href="#">PLA192, CPC1394, PLA193, PLA194</a>	High reliability and electrical isolation; robust design; no EMI / RFI generation	Up to 3750 V <sub>RMS</sub> input/output isolation; UL / IEC certified; low drive power
3	NTC	Sensing temperature of gas or water in specific meters	<a href="#">MELF style, End-banded Chip</a>	SMD form-factor allows for compact design; non-standards resistance values available	Surface mountable; fast thermal response
	Reed Switch	Sensing flow of gas or water	<a href="#">MDSR-10</a>	Lowest power consumption for longest battery life	Hermetically sealed; magnetically operated contacts
4	Reed Switch	Detects magnetically induced tampering	<a href="#">59166, 59177, MDSM-4, IMR</a>	Lowest power consumption for longest battery life	Hermetically sealed; magnetically operated contacts; available overmold for added robustness
	Detect Switch	Detects tampering of the meter casing	<a href="#">SDS, DDS</a>	Compact and reliable tamper detection	Low profile package; available in vertical and horizontal configurations; SMT or through-hole
5	Solid State Relay	Provides isolation from MCU and relief valve motor	<a href="#">PLA192, CPC1394, CPC1983YE, PLA193, PLA194</a>	High reliability & electrical isolation; robust design; no EMI / RFI generation	Up to 3750 V <sub>RMS</sub> input/output isolation; UL / IEC certified; low drive power
6	Tactile Switch	Switch for triggering display, resetting, etc.	<a href="#">KSC, KSE, PTS</a>	Available in wide range of operating forces; rugged sealing & resistant to corrosion; very long operating life	Ultra-low current consumption; operating life up to 1 million cycles

# Safety standards for electricity meters

Standard	Title	General scope	Market
<b>UL 2735</b>	Safety standard for Electric Utility Meters	These requirements cover the electrical safety of electric utility (revenue) meters rated up to 600 V, which measure, monitor, record, transmit, or receive electrical energy generation or consumption information.	United States
<b>ANSI C12.1</b>	Code for Electricity Metering	This Code is a reference for utilities, manufacturers, and regulatory bodies. It establishes acceptable performance criteria for new types of AC watthour meters, describes acceptable in-service performance levels for meters and devices used in revenue metering, and includes information on related subjects such as recommended measurements, installation requirements, test methods, and test schedules.	United States
<b>ANSI/IEEE C62.41.1</b>	Guide on the Surge Environment in Low-Voltage (1000 V and less) AC Power Circuits	Describes the mutual interactions between surge protective devices (SPDs) and power system disturbances.	United States
<b>ANSI/IEEE C62.41.2</b>	Recommended Practice on Characterization of Surges in Low-Voltage (1000 V and Less) AC Power Circuits	Provides guidance on how to assess by testing the effects of surges.	United States
<b>IEEE C62.45</b>	IEEE Recommended Practice on Surge Testing for Equipment Connected to Low-Voltage (1000 V and Less) AC Power Circuits		United States
<b>UL 2735C</b>	Electric Utility Meters for Canada	Similar to UL 2735.	Canada
<b>CAN3-C17-M84</b>	Alternating-Current Electricity Metering	Applies to the types of meters and associated devices normally used in the measurement of energy, power, or both in the supply and distribution of electricity as a commodity.	Canada

# Safety standards for electricity meters (cont'd)


Standard	Title	General scope	Market
<b>EN 62052 Series</b>	Electricity metering equipment – General requirements, tests, and test conditions	Similar to IEC 62052 Series.	Europe
<b>EN 62053 Series</b>	Electricity metering equipment – Particular requirements	Similar to IEC 62053 Series, with the exception of DC (part 41), not yet published by CENELEC.	Europe
<b>IEC 61000-4-2</b>	Electromagnetic compatibility (EMC) – Part 4-2: Testing and measurement techniques – Electrostatic discharge immunity test	This standard is made to check the capability of the equipment to survive repetitive electrical fast transients and bursts	Global
<b>IEC 61000-4-4</b>	Electromagnetic compatibility (EMC) – Part 4-4: Testing and measurement techniques – Electrical fast transient/burst immunity test	Evaluating the immunity of equipment when subjected to electrical fast transient/bursts on supply, signal, control, and earth ports.	Global
<b>IEC 61000-4-5</b>	Electromagnetic compatibility (EMC) – Part 4-5: Testing and measurement techniques – Surge immunity test	Evaluate the immunity of equipment when subjected to surges.	Global
<b>IEC 62052 Series</b>	Electricity metering equipment – General requirements, tests, and test conditions	This part of IEC 62052 covers type tests for electricity metering equipment for indoor and outdoor application and applies to newly manufactured equipment designed to measure the electrical energy on 50–60 Hz networks, with a voltage up to 600 V.	Global
<b>IEC 62053 Series</b>	Electricity metering equipment – Particular requirements	Part 21: Static meters for active energy (classes 1 & 2) Part 23: Static meters for reactive energy (classes 2 & 3) Part 24: Static meters for reactive energy at fundamental frequency (classes 0.5 S, 1 S, and 1) Part 41: Static meters for DC energy (classes 0.5 & 1) Part 61: Power consumption and voltage requirements	Global

# Safety standards for typical components in smart meters


		Standard	Title	General scope	Market
Component	Surge protection	UL 1449	Surge Protective Devices	Surge protective devices including MOVs shall comply with the requirements in the Standard for Surge Protection Devices.	United States
		UL 497B	Standard for Safety Protectors for Data Communications and Fire-Alarm Circuits	These requirements apply to TVS Diodes.	United States
	Overcurrent protection	UL 1434	Thermistor-Type Devices	Thermistors (PTCs and NTCs) shall comply with Standard for Thermistor-Type Devices.	United States
		UL 248-1	Standard for Safety Low-Voltage Fuses – Part 1: General Requirements	Fuses shall comply with Standards for fuses.	United States
		UL 248-14	Standard for Low-Voltage Fuses - Part 14: Supplemental Fuses		United States
	Battery	UL 1642	Lithium Batteries	Applicable standards that Li-ion batteries shall comply with.	United States
		UL 2054	Household and Commercial Batteries		United States
		IEC 62281	Safety of Primary and Secondary Lithium Cells and Batteries During Transport		Worldwide

# More information can be found at [Littelfuse.com](https://www.littelfuse.com)


Explore the world of Littelfuse with the electronic eCatalogs ([ecatalogs.littelfuse.com](https://ecatalogs.littelfuse.com))




Building Automation Guide





Circuit Protection Selection Guide



Sensor Selection Guide



Power Semiconductor Guide



Integrated Circuit Selection Guide



C&K Switches Selection Guide

# Local resources supporting our global customers



## Legend

- Sales
- R&D
- Manufacturing



# Partner for tomorrow's electronic systems

## Broad product portfolio

We are an industrial technology manufacturing company empowering a sustainable, connected, and safer world

## Application expertise

Our engineers partner directly with customers to help speed up product design and meet unique needs

## Global customer service

Our global customer service team will work with you to anticipate your needs and ensure a seamless experience

## Compliance & regulatory expertise

We help customers in the design process to account for requirements set by global regulatory authorities

## Testing capabilities

We help customers get products to market faster and offer certification testing to global regulatory standards

## Global manufacturing

We offer high-quality manufacturing that is committed to the highest quality standards





*This document is provided by Littelfuse, Inc. ("Littelfuse") for informational and guideline purposes only. Littelfuse assumes no liability for errors or omissions in this document or for any of the information contained herein. Information is provided on an "as is" and "with all faults" basis for evaluation purposes only. Applications described are for illustrative purposes only, and Littelfuse makes no representation that such applications will be suitable for the customer's specific use without further testing or modification. Littelfuse expressly disclaims all warranties, whether express, implied or statutory, including but not limited to the implied warranties of merchantability and fitness for a particular purpose, and non-infringement. It is the customer's sole responsibility to determine suitability for a particular system or use based on their own performance criteria, conditions, specific application, compatibility with other parts, and environmental conditions. Customers must independently provide appropriate design and operating safeguards to minimize any risks associated with their applications and products. Read complete Disclaimer Notice at [littelfuse.com/disclaimer-electronics](https://www.littelfuse.com/disclaimer-electronics).*



Expertise Applied | Answers Delivered

[Littelfuse.com](https://www.littelfuse.com)